

2.4GHz : Wi-Fi/BT External Antenna



PRO-EX-327

Request Samples



Check Inventory



Ø10 x 79 mm

RoHS/RoHS II Compliant

MSL Level = 1

Features

- Compact
- Gain of 3dBi
- Omni-directional Radiation pattern
- ROHS Compliant
- Easy to install
- Customizable Cable and Connector options

Applications

- Wi-Fi/Bluetooth/ZigBee/ISM
- IoT/M2M
- Network Devices
- Set top Boxes

Product Image



2.4GHz : Wi-Fi/BT External Antenna



PRO-EX-327

Request Samples



Check Inventory



Ø10 x 79 mm

RoHS/RoHS II Compliant

MSL Level = 1

Electrical Specification – Antenna

Parameter	Specification	Unit
Operating Frequency	2400 - 2500	MHz
Return Loss	< -13.5	dB
Polarization	Linear	-
Total Efficiency	> -1.4	dB
Peak Gain	2.7	dBi
Impedance	50	Ω

Note: Performance will vary depending on the ground plane, application, and environment.

Mechanical Specification

Parameter	Specification
Antenna Dimension	Ø10 x 79 mm
Mounting Type	Screw
Cable Type	Ø1.13 mm coaxial
Cable Length	100 ±5 mm
Connector Type	MHF-1 (F) (e.g. U.FL, IPEX)

Environmental Specification

Parameter	Specification
Storage Temperature	-30°C to +70°C



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-15-23

ABRACON IS
ISO9001-2015
CERTIFIED

2.4GHz : Wi-Fi/BT External Antenna



PRO-EX-327

Request Samples



Check Inventory




Ø10 x 79 mm

RoHS/RoHS II Compliant

MSL Level = 1


Product Dimensions



Unit: mm

Measurement Setup

The antenna measurements were all done in free space, assembled on an aluminum sheet metal test fixture according to the sketch below.



Unit: mm

2.4GHz : Wi-Fi/BT External Antenna



PRO-EX-327

Request Samples



Check Inventory




Ø10 x 79 mm


RoHS/RoHS II Compliant

MSL Level = 1

Reflection Characteristics – Return Loss



Radiation Characteristics – Total Efficiency (dB)



2.4GHz : Wi-Fi/BT External Antenna



PRO-EX-327

Request Samples



Check Inventory




Ø10 x 79 mm


RoHS/RoHS II Compliant

MSL Level = 1

Radiation Characteristics – Maximum Gain



Radiation Characteristics – 3D Pattern @ 2450 MHz



Unit: dBi



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-15-23

ABRACON IS
ISO9001-2015
CERTIFIED

2.4GHz : Wi-Fi/BT External Antenna



PRO-EX-327

Request Samples



Check Inventory





Ø10 x 79 mm

RoHS/RoHS II Compliant



MSL Level = 1

Radiation Characteristics – 2D Pattern @ 2450 MHz



XY-plane:



YZ-plane:



XZ-plane:



VP: Vertical Polarization
HP: Horizontal Polarization

Unit: dBi



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-15-23

ABRACON IS
ISO9001-2015
CERTIFIED

2.4GHz : Wi-Fi/BT External Antenna



PRO-EX-327

Request Samples



Check Inventory



Ø10 x 79 mm

RoHS/RoHS II Compliant

MSL Level = 1

Packaging

The antenna is delivered in a plastic bag.

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-15-23

ABRACON IS
ISO9001-2015
CERTIFIED