

S12LOC-P12MFD0-5200  
series\_l  
type\_s1





General information

|                   |                     |
|-------------------|---------------------|
| Part number       | S12LOC-P12MFD0-5200 |
| Termination       | solder              |
| Size              | 2                   |
| Locking principle | push                |
| Coding            | 0_key               |
| Cable Diameter    | cable_mini_52       |
| Cable outlet      | standard            |



Illustrations may differ from original product.  
Dimensions, unless otherwise specified, in mm.



The pin layout corresponds to the view on the termination area

Contact insert description

|                      |        |
|----------------------|--------|
| Number of contacts   | 12     |
| Contact type         | pins   |
| Contact diameter     | 07mm   |
| Insulator material   | peek   |
| Wire cross section   | 26_awg |
| Termination          | solder |
| Termination diameter | 065mm  |

reverse\_gender\_on\_request

Technical information

|                                          |           |               |
|------------------------------------------|-----------|---------------|
| Max. creepage and air clearance distance | 10_mm     | 13_mm         |
| Nominal current single contact           | 06_a      | iec_60512_5_2 |
| Nominal current insert                   | 3,3 A     | vde_0298_4    |
| Test voltage                             | 135_kv_ac | sae_13441     |

safety\_text

**Mechanical and environmental data**

|                       |          |
|-----------------------|----------|
| Degree of protection* | ip50     |
| Operating temperature | 40_120_c |
| Mating cycles         | 5000     |

mated\_unmated

**Material and surface treatments**

|         |               |
|---------|---------------|
| Housing | m_chrome      |
| Contact | cu_alloy_gold |

safety\_text\_2  
ul\_text  
illustrative\_text