

safety module, Harmony XPS, estop or guard, connected to supply terminals 48 to 240V AC or DC, no inputs, spring

XPSBAC34AC

Main

Range of product	Harmony Safety Automation				
Product or component type Safety module					
Safety module name	XPSBAC				
Safety module application	For emergency stop and protective guard applications				
Function of module	Emergency stop button with 2 NC contacts Guard monitoring with 1 or 2 limit switches				
Safety level	Can reach PL e/category 4 for normally open relay contact conforming to ISO 13849-1 Can reach SILCL 3 for normally open relay contact conforming to IEC 62061 Can reach SIL 3 for normally open relay contact conforming to IEC 61508 Can reach PL c/category 1 for normally closed relay contact conforming to ISO 13849-1 Can reach SILCL 1 for normally closed relay contact conforming to IEC 62061 Can reach SIL 1 for normally closed relay contact conforming to IEC 61508				
Safety reliability data	MTTFd > 30 years conforming to ISO 13849-1 for normally open relay contact Dcavg >= 99 % conforming to ISO 13849-1 for normally open relay contact PFHd = 1.01E-09 conforming to ISO 13849-1 for normally open relay contact HFT = 1 conforming to IEC 62061 for normally open relay contact PFHd = 1.01E-09 conforming to IEC 62061 for normally open relay contact PFHd = 1.01E-09 conforming to IEC 62061 for normally open relay contact SFF > 99% conforming to IEC 61508-1 for normally open relay contact PFHd = 1.01E-09 conforming to IEC 61508-1 for normally open relay contact SFF > 99% conforming to IEC 61508-1 for normally open relay contact SFF > 99% conforming to IEC 61508-1 for normally open relay contact Type = B conforming to IEC 61508-1 for normally open relay contact MTTFd > 30 years conforming to ISO 13849-1 for normally closed relay contact DC > 60 % conforming to ISO 13849-1 for normally closed relay contact PFHd = 1.01E-09 conforming to ISO 13849-1 for normally closed relay contact HFT=0 conforming to IEC 62061 for normally closed relay contact SFF > 60% conforming to IEC 62061 for normally closed relay contact HFT=0 conforming to IEC 62061 for normally closed relay contact HFT=0 conforming to IEC 61508-1 for normally closed relay contact HFT=0 conforming to IEC 61508-1 for normally closed relay contact SFF > 60% conforming to IEC 61508-1 for normally closed relay contact SFF > 60% conforming to IEC 61508-1 for normally closed relay contact Type = B conforming to IEC 61508-1 for normally closed relay contact				
Electrical circuit type	NC pair				
Connections - terminals	Removable spring terminal block, 0.22.5 mm² solid or flexible Removable spring terminal block, 0.252.5 mm² flexible with ferrule single conductor Removable spring terminal block, 0.21.5 mm² solid or flexible twin conductor Removable spring terminal block, 2 x 0.251 mm² flexible with ferrule without cable end, with bezel Removable spring terminal block, 2 x 0.51.5 mm² flexible with ferrule with cable end, with bezel				
Us] rated supply voltage 48240 V AC - 1510 % 48240 V DC - 2020 %					

Complementary

Synchronisation time between inputs	Unlimited		
Type of start	Automatic/manual/monitored		

Power consumption in W	2.0 W 48240 V DC			
Power consumption in VA	6.0 VA 48240 V AC 50/60 Hz			
Input protection type	Internal, electronic			
safety outputs	4 NO + 1 NC			
safety inputs	0			
Input compatibility	Normally closed circuit conforming to ISO 14119			
	XC limit switch conforming to ISO 14119			
	Mechanical contact conforming to ISO 14119 Normally closed circuit conforming to ISO 13850			
input terminal	Power supply			
[le] rated operational current	5 A AC-1 for normally open relay contact			
	3 A AC-15 for normally open relay contact			
	5 A DC-1 for normally open relay contact			
	3 A DC-13 for normally open relay contact			
	3 A AC-1 for normally closed relay contact			
	1 A AC-15 for normally closed relay contact			
	3 A DC-1 for normally closed relay contact			
	1 A DC-13 for normally closed relay contact			
control outputs	0			
[Ith] conventional free air thermal current	al 6A			
Associated fuse rating	10 A gG for NO relay output circuit conforming to IEC 60947-1			
Minimum output current	10 mA for relay output			
Minimum output voltage	5 V for relay output			
Response time	60 ms at 48240 V AC/DC			
[Ui] rated insulation voltage	300 V (pollution degree 2) conforming to IEC 60947-1			
[Uimp] rated impulse withstand voltage	4 kV overvoltage category II conforming to IEC 60947-1			
Local signalling	LED green with power marking for power ON			
	LED red with error marking for error			
	LED yellow with state marking for status			
	LED yellow with start1 marking for start input LED yellow with start2 marking for start input			
	LED YOUNDW WITH STATE THATKING TOLESTATE HIPUT			
Mounting support	35 mm symmetrical DIN rail			
Depth	120 mm			
Height	100 mm			
Width	22.5 mm			
Product weight	0.200 kg			
Environment				
Ambient air temperature for operation	-2555 °C			
Standards	IEC 60947-5-1			
	IEC 61508-1 functional safety standard			
	IEC 61508-2 functional safety standard			
	IEC 61508-3 functional safety standard			

Ambient air temperature for operation	-2555 °C			
Standards	IEC 60947-5-1			
	IEC 61508-1 functional safety standard			
	IEC 61508-2 functional safety standard			
	IEC 61508-3 functional safety standard			
	IEC 61508-4 functional safety standard			
	IEC 61508-5 functional safety standard			
	IEC 61508-6 functional safety standard			
	IEC 61508-7 functional safety standard			
	ISO 13849-1 functional safety standard			
	IEC 62061 functional safety standard			
Product certifications	TÜV			
	cULus			

IP degree of protection	IP20 (terminals) conforming to IEC 60529 IP40 (housing) conforming to IEC 60529 IP54 (mounting area) conforming to IEC 60529
Relative humidity	595 % non-condensing

Packing Units

Unit Type of Package 1	PCE		
Number of Units in Package 1	1		
Package 1 Height	6.900 cm		
Package 1 Width	13.500 cm		
Package 1 Length	15.700 cm		
Package 1 Weight	317.000 g		
Unit Type of Package 2	S03		
Number of Units in Package 2	16		
Package 2 Height	30.000 cm		
Package 2 Width	30.000 cm		
Package 2 Length	40.000 cm		
Package 2 Weight	5.812 kg		



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	71
Environmental Disclosure	Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	152cf799-1df7-4892-81b4-4c890187f1d1
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions

Front and Side Views



(A): Product drawing
(B): Spring terminal

(C): Side view

(1): Removable terminal blocks, top(2): Removable terminal blocks, bottom


(3): LED indicators

(4) : Sealable transparent cover


mm in.	0.47					
	mm²	0,22,5	0,252,5	0,21,5	0,251	0,51,5
	AWG	2412	2412	2416	2418	2016

Mounting and Clearance

Mounting to DIN rail




Screw-mounting



Connections and Schema

Wiring Diagram



(1): A1-A2 (Power supply)
(2): Y1 (Control output of Start/Restart input), Y2 (Input channel for automatic/manual start/restart), Y3 (Input channel for monitored start/restart with falling edge)

13-14-23-24-33-34-43-44-51/61-52-62 : Terminals of the safety-related outputs

Image of product / Alternate images

Alternative



