

Advanced touchscreen panel, Harmony GTO, 12.1 Color Touch SVGA TFT, coated display

HMIGTO6310FC

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony GTO	
Product or Component Type	Advanced touchscreen panel	
Display colour	65536 colours	
Display size	12.1 inch	
Supply	External source	
Battery type	Lithium internal RAM 100 days 5 day(s) 10 year(s)	

Complementary

Touchscreen display Backlit colour TFT LCD	
Backlit colour TFT LCD	
800 x 600 pixels SVGA	
1024 x 1024	
Resistive film, 1000000 cycles	
50000 hours white 77 °F (25 °C)	
16 levels by touch panel 16 levels by software	
Japanese (ANK, Kanji) Taiwanese (traditional Chinese) Korean Chinese (simplified Chinese) ASCII (European characters)	
24 V DC	
19.228.8 V	
30 A	
12 W when power is not supplied to external devices 7 W when backlight is OFF 8 W when backlight is dimmed 17 W	
Status LED green, steady offline Status LED green, steady operating Status LED orange, flashing software starting up Status LED red, steady power supply (ON) Status LED clear, faded power supply (OFF) COM2 LED yellow, steady data is being transmitted COM2 LED yellow, faded no data transmission SD card LED green, steady card is inserted SD card LED green, faded card is not inserted or is not being accessed	
Vijeo Designer configuration software >= V6.1	
Flash EPROM, 96 MB	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Data backed up	512 KB internal RAM SRAM)	
Data storage equipment	SD card, <= 32 GB SDHC card, <= 32 GB	
Downloadable protocols	Schneider Electric Modicon Modbus Schneider Electric Modicon Uni-TE Schneider Electric Modicon Modbus Plus Schneider Electric Modicon FIPWAY Mitsubishi Melsec third party protocols Omron Sysmac third party protocols Rockwell Automation Allen-Bradley third party protocols Siemens Simatic third party protocols Schneider Electric Modicon Modbus TCP	
Integrated connection type	COM1 serial link SUB-D 9 RS232C 2400115200 bps COM2 serial link RJ45 RS485 2400115200 bps COM2 serial link RJ45 RS485 187.5 kbps Siemens MPI Ethernet RJ45 10BASE-T/100BASE-TX Ethernet RJ45 IEEE 802.3 USB 2.0 type A USB 2.0 type mini B	
Product mounting	Flush mounting	
Fixing mode	by 4 screw clamps	
Front material	PPT	
Enclosure Material	PPT	
Type of cooling	Natural convection	
Width	12.4 in (315 mm)	
Height	9.5 in (241 mm)	
Depth	2.2 in (56 mm)	
Product Weight	5.5 lb(US) (2.5 kg)	
Environment		
Standards	UL 508 IEC 61131-2 IEC 61000-6-2	
Product Certifications	KCC CE cULus C-tick UKCA UKEX	
Ambient Air Temperature for Operation	32131 °F (055 °C)	
Ambient air temperature for storage	-4140 °F (-2060 °C)	
Relative humidity	1090 % without condensation	
Operating altitude	< 6561.68 ft (2000 m)	
IP degree of protection	IP20 IEC 60529 rear panel) IP65 IEC 60529 front panel)	
NEMA degree of protection	NEMA 4X front panel (indoor use)	
Observation and the same of		

Ordering and shipping details

Category US10MC222569

Shock resistance

Vibration resistance

Resistance to electrostatic discharge

147 m/s² 3 chocks in each direction X, Y and Z IEC 61131-2

6 kV contact discharge IEC 61000-4-2 level 3

3.5 mm 5...9 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - IEC 61131-2 1 gn 9...150 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - IEC 61131-2

Discount Schedule	0MC2
GTIN	3606480841811
Returnability	No
Country of origin	CN

Packing Units

r adming dimes		
Unit Type of Package 1	PCE	
Nbr. of units in pkg.	1	
Package 1 Height	6.77 in (17.2 cm)	
Package 1 Width	12.80 in (32.5 cm)	
Package 1 Length	15.35 in (39.0 cm)	
Package weight(Lbs)	7.14 lb(US) (3.24 kg)	
Unit Type of Package 2	CAR	
Number of Units in Package 2	2	
Package 2 Height	16.93 in (43.0 cm)	
Package 2 Width	13.98 in (35.5 cm)	
Package 2 Length	17.91 in (45.5 cm)	
Package 2 Weight	15.862 lb(US) (7.195 kg)	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	907	
Environmental Disclosure	Product Environmental Profile	

Use Better

Materials and Substances	
F-gas usage performance	Only air and vacuum used for insulation / breaking, no F-gas including SF6
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	3647523b-250a-4687-bcce-2d1cdcab982a
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds
PVC free	No
Silicon free	No

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.