

GVSUPS40KR0B5HS

Galaxy VS UPS 40kW 400V with N+1 power module, for 5 smart modular 9Ah battery strings, Start-up 5x8



Overview

Presentation	Highly efficient, easy-to-deploy 40kW, 400V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. This UPS is for up to 5 smart modular high capacity battery strings, but is supplied without batteries, so you can easily customize the battery runtime. Includes 5x8 start-up service and one additional power module for N+1 redundancy.
Lead time	Usually Ships within 2 Weeks

Main

Main Input Voltage	3 phase
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phase
Other Output Voltage	380 V 415 V
Kw Rating	40 kW
Rated power in VA	40 kVA
Battery Type	Internal modular battery VRLA
Provided equipment	Dust filter Installation manual Integrated network management Start-Up Service EcoStruxure Ready

General

Redundant	No
-----------	----

Physical

Color	White
Height	77.56 in (197 cm)
Width	21.65 in (55 cm)
Depth	33.35 in (84.7 cm)
Net Weight	652.57 lb(US) (296 kg)
USB compatible	No

Input

Input Frequency	40 - 70 Hz
Efficiency at full load	340...460 V 400 V
Maximum Input Current per Phase	72 A
Maximum Short Circuit Withstand (Icw)	65 kA
Input Total Harmonic Distortion	Less than 6 % for full load

Load power factor	From 0.7 leading to 0.7 lagging without any derating
Input Power Factor at Full Load	0.99

Output

Max Configurable Power (Watts)	40 kW
Harmonic distortion	Less than 3%
Output Frequency (sync to mains)	50 Hz sync to mains 60 Hz sync to mains
Crest factor	2.5
Waveform Type	Sine wave
Output voltage tolerance	+/- 5% after 2ms +/-1% after 50ms
Output Voltage THD	< 1% linear load and < 3% non-linear load
Overload Operation	10 minutes @ 125% and 60 seconds @ 150%
Bypass type	Built-in Static Bypass
Maximum configurable power in VA	40 kVA

Conformance

Standards	IEC 62040-1-1 IEC 62040-2 OSHPD
-----------	---------------------------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...3300 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	10...80 % Non-condensing
Storage altitude	0...10000 ft (0.00...3048.00 m)
Acoustic level	54 dBA
Heat dissipation	4412 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Battery Voltage	480V
End of Discharge Battery Voltage	384 V
End of Discharge Maximum Battery Current	109 A
Battery power in VAh	0 VAh runtime
Extendable Run Time	0

Communications & Management

Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity

Ordering and shipping details

GTIN	731304410133
Package weight(Lbs)	551.16 lb(US) (250 kg)

Packing Units

Package 1 Height	81.97 in (208.2 cm)
Package 1 width	29.72 in (75.5 cm)
Package 1 Length	39.76 in (101 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---