

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

|                           |                                 |
|---------------------------|---------------------------------|
| Range of product          | Harmony 9001K                   |
| Product or component type | Illuminated selector switch     |
| Device short name         | 9001K                           |
| Type of operator          | Spring return (right to centre) |
| Operator profile          | Standard knob amber             |

## Complementary

|                               |                          |
|-------------------------------|--------------------------|
| Bezel material                | Chromium plated metal    |
| Mounting diameter             | 1.18 in (30 mm)          |
| Product weight                | 0.54 lb(US) (0.245 kg)   |
| Shape of signaling unit head  | Round                    |
| Operator position information | 3 positions              |
| Contacts type and composition | Without contact block    |
| Mechanical durability         | 500000 cycles            |
| Light block supply            | Via integral transformer |
| Light source                  | Incandescent             |
| Bulb base                     | BA 9s                    |
| [Us] rated supply voltage     | 110...120 V AC 50/60 Hz  |
| Device presentation           | Basic element            |

## Environment

|                                       |  |
|---------------------------------------|--|
| Protective treatment                  | TC   |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)   |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)   |
| Electrical shock protection class     | Class II conforming to IEC 61140   |
| IP degree of protection               | IP66 conforming to IEC 60529   |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 6                                |
| Standards                             | EN/IEC 60947-1<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>JIS C 4520<br>JIS C 852<br>UL 508<br>CSA C22.2 No 14 |
| Product certifications                | NEMA<br>UL 508   |
| Vibration resistance                  | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6  |
| Shock resistance                      | 50 gn conforming to IEC 60068-2-27   |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| GTIN                  | 00785901229094                |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.5                           |
| Returnability         | N                             |
| Country of origin     | MX                            |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| California proposition 65  | WARNING: This product can expose you to chemicals including:   |
| - - - - - Substance 1      | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| - - - - - More information | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                    |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|