




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L1	REVISED PER ECN-24-281974	29AUG2024	RK	ASC




- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 2 ASSEMBLIES MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 3 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 4 .000050 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 .000050 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 6 HIGH TEMPERATURE CONFIGURATION
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

7 OBSELETE	6	5	3.984	3.900	39	80	9-103739-0
	6	5	1.584	1.500	15	32	6-103739-6
	6	5	1.484	1.400	14	30	6-103739-5
	6	5	1.184	1.100	11	24	6-103739-2
	6	5	.984	.900	9	20	6-103739-0
	6	5	.484	.400	4	10	5-103739-5
	6	5	.184	.100	1	4	5-103739-2
		4	3.984	3.900	39	80	4-103739-0
OBSELETE			3.884	3.800	38	78	3-103739-9
OBSELETE			3.784	3.700	37	76	3-103739-8
OBSELETE			3.684	3.600	36	74	3-103739-7
OBSELETE			3.584	3.500	35	72	3-103739-6
OBSELETE			3.484	3.400	34	70	3-103739-5
OBSELETE			3.284	3.300	33	68	3-103739-4
OBSELETE			3.284	3.200	32	66	3-103739-3
OBSELETE			3.184	3.100	31	64	3-103739-2
OBSELETE			3.084	3.000	30	62	3-103739-1
OBSELETE			2.984	2.900	29	60	3-103739-0
OBSELETE			2.884	2.800	28	58	2-103739-9
OBSELETE			2.784	2.700	27	56	2-103739-8
OBSELETE			2.684	2.600	26	54	2-103739-7
OBSELETE			2.584	2.500	25	52	2-103739-6
OBSELETE			2.484	2.400	24	50	2-103739-5
OBSELETE			2.384	2.300	23	48	2-103739-4
OBSELETE			2.284	2.200	22	46	2-103739-3
OBSELETE			2.184	2.100	21	44	2-103739-2
OBSELETE			2.084	2.000	20	42	2-103739-1
OBSELETE			1.984	1.900	19	40	2-103739-0
OBSELETE			1.884	1.800	18	38	1-103739-9
OBSELETE			1.784	1.700	17	36	1-103739-8
OBSELETE			1.684	1.600	16	34	1-103739-7
7 OBSELETE		4	1.584	1.500	15	32	1-103739-6
7 OBSELETE		4	1.484	1.400	14	30	1-103739-5
OBSELETE			1.384	1.300	13	28	1-103739-4
OBSELETE			1.284	1.200	12	26	1-103739-3
7 OBSELETE		4	1.184	1.100	11	24	1-103739-2
OBSELETE			1.084	1.000	10	22	1-103739-1
7 OBSELETE		4	.984	.900	9	20	1-103739-0
OBSELETE			.884	.800	8	18	103739-9
OBSELETE			.784	.700	7	16	103739-8
OBSELETE			.684	.600	6	14	103739-7
OBSELETE			.584	.500	5	12	103739-6
7 OBSELETE		4	.484	.400	4	10	103739-5
OBSELETE			.384	.300	3	8	103739-4
OBSELETE			.284	.200	2	6	103739-3
7 OBSELETE		4	.184	.100	1	4	103739-2
OBSELETE			.084			2	103739-1
	REMARKS	PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L D RINGLEY 25-07-85		 TE Connectivity			
			CHK R ELICKER 26-07-85					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R ELICKER 26-07-85		NAME ASSEMBLY, MOD II, HEADER, BREAKAWAY, DR, .100X, 100 C/L, WITH .025 SQUARE POSTS		
		0 PLC ± -		PRODUCT SPEC				
		1 PLC ± -		—				
		2 PLC ± -		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
		3 PLC ± .005		—				
		4 PLC ± -		WEIGHT		A2 00779 C=103739 —		
		ANGLES ± -		—				
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR: BLACK CONTACT: COPPER ALLOY		FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 1 REV L1		