

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2015

© COPYRIGHT 1999

BY TE CONNECTIVITY


ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-14-019072	23FEB2015	JA	DM
	C1	REVISED PER PCN-24-213773	02JUL2024	HD	CB
	D	REVISED PER PCN-24-219306	29AUG2024	CO	CB
	E	REVISED PER PCN-25-233228	19DEC2024	RK	CB



7 LOCATIONS FOR TRACEABILITY WITNESS MARKS ONLY

6. PART MODIFICATION: THREADED ADAPTER


5 CONDUIT ADAPTER ACCEPTS EITHER TYPES:
A. CONDUIT ADAPTER CAP NUT (CN21) AND SEAL RING (SRN21)
B. BACKSHELL (M902-2243), COMPRESSION NUT (M902-2053), CABLE Ø.430-.570 [10.92-14.78]
C. BACKSHELL (M902-2244), COMPRESSION NUT (M902-2054), CABLE Ø.570-710 [14.78-18.03]

4 MATERIAL: PLUG HOUSING/COUPLING RING: PA66 GF10 (BLACK)
CONDUIT ADAPTER: PA66 GF10 (GREEN, GRAY, BLUE)
GROMMET: SILICONE (ORANGE-RED)


3 SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOLS

2. THIS PLUG MATES WITH HDP24-24XXP/SX-XXXX RECEPTACLE
X = SEAL TYPE (N,T,E)
XX = INSERT ARRANGEMENT
XXXX = MODIFICATION

1 SEE CUSTOMER DRAWING 0425-014-2400 FOR AVAILABLE INSERT ARRANGEMENTS AND PART NUMBERS.



SCALE 1:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19JAN1999 STEVE BEARD		 TE Connectivity				
DIMENSIONS: INCHES[mm]		CHK 15JAN2001 STEVE BEARD						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.015 [0.38] 4 PLC ± ANGLES ±0°30'0"		APVD 15JAN2001 STEVE BEARD		NAME PLUG, COUPLING RING SIZE 24, -L015 MOD HDP SERIES			
			PRODUCT SPEC 0425-021-0000					
			APPLICATION SPEC 					
MATERIAL 	FINISH N/A		WEIGHT		SIZE A3	CAGE CODE 4AFU8	DRAWING NO G-HDP26-24-XXP/SX-L015	RESTRICTED TO -
Customer Drawing						SCALE 2:1	SHEET 1 OF 1	REV E