



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Cannot be Certified**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free


Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1490747-1 HYP10 HEAVY DUTY 12T HEAD	 TE Part # 321873 BODY SOLIS RING 2/0 1/2	 TE Part # 322225 TERMINAL,SOLIS R 2/0 3/4	 TE Part # 36948 SPLICE,SOLIS PARA 2/0
 TE Part # 36925 TERMINAL,SOLIS R 2/0 1/2	 TE Part # 132074-2 TERM, SOLIS, RT, 2/0, M8(5/16)	 TE Part # 321872 TERMINAL,SOLIS R 2/0 7/16	 TE Part # 321873-2 STRATO-THERM, HR 2/0 1/2 NIPL
 TE Part # 321870 TERMINAL SOLIS R 2/0 5/16	 TE Part # 160001 TERM,SOLIS R 2/0 M10	 TE Part # 1490746-1 HYP10 LIGHT DUTY 14T HEAD	 TE Part # 1490745-1 HYP10 LIGHT DUTY 12T HEAD



TE Part # 321871-2
STRATO-THERM, HR 2/0 3/8 NIPL



TE Part # 36958
SPLICE,SOLIS BUTT 2/0



TE Part # 321871
BODY SOLIS RING 2/0 3/8



TE Part # 36921
TERMINAL,SOLIS R 2/0 1/4



TE Part # 36922
TERMINAL,SOLIS R 2/0 5/16



TE Part # 36923
TERMINAL,SOLIS R 2/0 3/8




TE Part # 1490749-1
HYP10 8-4/0AWG MANUAL TOOL



TE Part # 321869
TERMINAL,SOLIS R 2/0 1/4

Customers Also Bought



TE Part #144469-000
FLHTC0311-16-9




TE Part #31808
TERMINAL,SOLIS R 8 5/16



TE Part #33115
TERMINAL,SOLIS R 4 5/16



TE Part #33464
TERMINAL,SOLIS R 6 10



TE Part #52594-2
AMPOWER DISC 1/0 AG W/SIGHT HO



TE Part #2-320576-1
TERMINAL,PIDG R 12-10 5/16




TE Part #322246
SPLICE,SOLIS BUTT 2



TE Part #726348-2
SO-RINGZUNGE D46234



TE Part #1490414-2
HYP10 SOLIS HD 6-4AWG INDENTER



TE Part #8-1617760-3
FCB-405-0622M=M83536/6-022M

Documents



Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English