




Application Tooling > Heat Shrink Equipment



Equipment Processing Type: **Discrete**

Applicable Region: **Worldwide**

Heat Shrink Equipment Application: **In-Line Splice, Ring Terminal, Stub Splice**

Tooling Type: **Heating Tool**

Spare Parts Tooling Type: **RBK Processor**

Features

Product Type Features

Spare Parts Tooling Type	RBK Processor
--------------------------	---------------

Dimensions

Tubing Outer Diameter (Max)	≤ 19 mm[≤ .75 in]
Tubing Length (Max)	≤ 65 mm[≤ 2.56 in]

Product Availability

Applicable Region	Worldwide
-------------------	-----------

Other

Equipment Processing Type	Discrete
Heat Shrink Equipment Application	In-Line Splice, Ring Terminal, Stub Splice
Tooling Type	Heating Tool
Substrate Outside Diameter Max	9.5 mm

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 4-2234788-8 CABLE FLATNESS KEEPER, LEFT	TE Part # 8-529533-2 DOUBLE FIXTURE ID 4.5MM	TE Part # 7-2234788-2 CABLE CLAMPER, RIGHT	 TE Part # 1-2234800-1 RBK-X1, AUTO TRIGGER
TE Part # 6-529533-1 FIXTURE ID 4.5MM CPL.	TE Part # 7-2234788-3 CABLE CLAMPER, CIRCLE	TE Part # 7-2234788-7 KIT, TERMINAL HOLDER, RBK	TE Part # 7-2234788-4 END CAP HOLDER, DUAL





TE Part # 2234800-1
RBK-X1 STD

TE Part # 4-2234788-7
CABLE FLATNESS KEEPER, RIGHT

TE Part # 7-2234788-1
CABLE CLAMPER, LEFT


TE Part # 4-2234788-9
END CAP HOLDER

TE Part # 7-2234788-0
STANDARD TOOL KIT

TE Part # 6-2234788-8
CABLE CLAMPER, FLATTEN



TE Part # 1-2234800-3
RBK-X1, W/ AIR COOLING



TE Part # 2384437-1
KIT, TERMINAL HOLDER, RBK


TE Part # 8-529533-3
DOUBLE FIXTURE ID 5.5MM

TE Part # 8-529533-4
DOUBLE FIXTURE ID 8MM

TE Part # 6-529533-3
FIXTURE ID 8MM CPL.

TE Part # 6-529533-2
FIXTURE ID 5.5MM CPL.

Customers Also Bought



TE Part #CAT-T3437-T548
TMS-SCE Military Grade Sleeves

TE Part #8-509416-6
SET CLAMPING ELEMENTS, WIRES

TE Part #1-509871-2
TOOTHED BELT AT5B10L320

Documents

Product Drawings

RBK FIXTURE, MULTI-TOOL, A/C

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

French



[Instruction Sheet \(non U.S.\)](#)

[Instruction Sheet \(non U.S.\)](#)

[Instruction Sheet \(non U.S.\)](#)

[Instruction Sheet \(non U.S.\)](#)

[Instruction Sheet \(non U.S.\)](#)

[Instruction Sheet \(non U.S.\)](#)

German

Agency Approvals

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

English

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

French

[CE Declaration of Conformity](#)

German