



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Board-to-Board**
Connector Mounting Type: **Board Mount**
Number of Positions: **8**
Connector & Contact Terminates To: **Printed Circuit Board**
Contact Current Rating (Max): **2 A**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Circular Connector Type	Plug

Configuration Features

Number of Positions	8
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	30 VDC
-------------------	--------

Body Features

Entry Style	Side
Environmental Protection	IP67

Contact Features

--	--



Contact Current Rating (Max)	2 A
Circular Connector Contact Type	Pin

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Mating Alignment	With
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Polarization Code	A
Mating Alignment Type	Polarization
Mating Retention	Without

Usage Conditions

Operating Temperature Range	-25 – 85 °C[-13 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 225521-E
M12 MALE, A CODE,RA, 8P THR
FRONT MOUNT



TE Part # 464272-E
M12 METAL SHELL, MALE, VERT, 9MM




TE Part # 394863-E
M12 METAL SHELL, MALE, VERT,
13MM, D9.55



TE Part # T4112012081-000
M12 F, 8P GOLD A_CODE RA
SHIELDED PG9



TE Part # T4110012081-000
M12 F, 8P GOLD A_CODE S
SHIELDED PG9



TE Part # 374342-E
MRDBG R M12 M ***** J 2 374342
ABDE



TE Part # 284377-E
M12 METAL SHELL, MALE, VERT,
13MM, D8.35




TE Part # T4161320008-001
RPC-M12-FS-8CON-PUR-0.5SH



TE Part # 225516-E
M12 MALE, A CODE, RA, 4P THR
FRONT MOUNT


Also in the Series | M12 Connector



Connector Hardware(11)



Connector Seals & Cavity Plugs(4)



M8/M12 Cable Assemblies(230)



Standard Circular Connectors(792)

Customers Also Bought



TE Part #F99802-000
S200-3-W1-22-9



TE Part #474339-E
IDCTERM 1 I2426 1,10 * 167 707 0007 J 2



TE Part #CJ8360-000
S200-2-W2-22-9



TE Part #354130-E
M12 MALE, B CODE, 5P, 10.5MM SMT



TE Part #474771-E
M12 FEMALE, X CODE, 8P, 17MM SMT, CAT6A



TE Part #839016-E
IDCCS SRC 1,27 4 * SFX SFX 100 PVC



TE Part #CB5407-000
SST-6-04/FR/97



TE Part #1-316132-5
DYNAMIC D-3200 HDR ASSY 5P V



TE Part #2-520128-2
ULTRA-FAST 250 ASY REC 22-18 AWG TPBR



TE Part #2351445-4
UMINSA SW HLV0.88N 3A/1.5A AC SC PCB

Documents

Product Drawings

M12 MALE, A CODE,RA, 8P THR REAR MOUNT

English

CAD Files

Customer View Model

ENG_CVM_CVM_225614-E_1.3d_igs.zip

English

Customer View Model



[ENG_CVM_CVM_225614-E_1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_225614-E_1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English