




Automotive Parts > Automotive Cable Assemblies > Infotainment & Multimedia Cable Assemblies



Cable Type: RTK 031

Shielded: Yes

Impedance: 50 Ω

Sealable: No

Cable Assembly Length: 3 m [9.84 ft]

Features

Product Type Features

Sealable	No
----------	----

Electrical Characteristics

Operating Voltage	60 VDC
Impedance	50 Ω

Usage Conditions

Cable Type	RTK 031
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Shielded	Yes
----------	-----

Other

Cable Assembly Length	3 m[9.84 ft]
-----------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2321775-5
4P,MATE-AX,HDR ASSY,90DEG,COD E



TE Part # 2298721-9
4P,MATE-AX,SOC HSG ASSY,180DEG,COD Z



TE Part # 2304168-6
4P MATE-AX, HDR ASSY,90 DEG,COD F



TE Part # 2321775-3
4P,MATE-AX,HDR ASSY,90DEG,COD C



TE Part # 2304168-9
4P MATE-AX, HDR ASSY,90 DEG,COD Z



TE Part # 2304168-3
4P MATE-AX, HDR ASSY,90 DEG,COD C



TE Part # 2321775-4
4P,MATE-AX,HDR ASSY,90DEG,COD D



TE Part # 2321775-2
4P,MATE-AX,HDR ASSY,90DEG,COD B





TE Part # 2304168-5
4P MATE-AX, HDR ASSY, 90 DEG, CODE



TE Part # 2321775-1
4P, MATE-AX, HDR ASSY, 90 DEG, CODE A



TE Part # 2321775-6
4P, MATE-AX, HDR ASSY, 90 DEG, CODE F



TE Part # 1-1452584-1
1 WAY PLUG CONN FAKRA2



TE Part # 2304168-4
4P MATE-AX, HDR ASSY, 90 DEG, CODE D



TE Part # 2321775-9
4P, MATE-AX, HDR ASSY, 90 DEG, CODE Z




TE Part # 2304168-2
4P MATE-AX, HDR ASSY, 90 DEG, CODE B




TE Part # 2304168-1
4P MATE-AX, HDR ASSY, 90 DEG, CODE A


Customers Also Bought




TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts




TE Part #DT06-2S
PLG, 2P, GRY, N




TE Part #DT04-2P
REC, 2P, GRY, N




TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING

Documents

Product Drawings
MATE-AX/FAKRA II,CABLE ASSY
English

CAD Files
Customer View Model
ENG_CVM_CVM_2360001-4_A.3d_igs.zip
English
Customer View Model



[ENG_CVM_CVM_2360001-4_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2360001-4_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English