



Automotive Parts > Automotive Connectors > Automotive Housings > DC Fast Charge CCS1 and CCS2 Inlet Kits



Connector & Housing Type: **Housing for Male Terminals**

Number of Positions: **7**

Sealable: **Yes**

Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Connector Position Assurance Capable: **No**

[All DC Fast Charge CCS1 and CCS2 Inlet Kits \(24\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector System	Wire-to-Panel
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	7
---------------------	---

Electrical Characteristics

Nominal Voltage Architecture	250 V
------------------------------	-------

Body Features

Cable Exit Angle	90°
------------------	-----



Primary Product Color

Black

Contact Features

Contact Current Rating (Max)	32 A, 200 A
------------------------------	-------------

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Dimensions

Product Width	132.5 mm[5.21 in]
Product Length	126 mm[4.96 in]
Connector Height	156.1 mm[6.14 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
Operating Temperature (Max)	85 °C[185 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

IP Rating	IP67
-----------	------

Packaging Features

Packaging Method	Box
Packaging Quantity	1


Other

Connector Position Assurance Capable	No
--------------------------------------	----

Compatible Parts



TE Part # 2296057-2
COVER, CABLE SEAL, AC



TE Part # 2276149-6
Large Size Wire Applicator-LP



TE Part # 2151022-1
OCEAN_2.0_APPLICATOR-S-055F070F-RSM




TE Part # 2293269-3
DIA 6MM,PIN TERMINAL



TE Part # 1-967640-1
4POS MQS REC COD A

Also in the Series | Charging Inlets



Automotive Connector Locks & Position Assurance(1)



Automotive Housings(30)



Automotive Seals & Cavity Plugs(5)




Electric, Hybrid & Fuel Cell Cable Assemblies(101)

Customers Also Bought



TE Part #CAT-55A-TC-H24
General Purpose Hookup Wire: Tin Coated Copper Wire, 24 AWG




TE Part #820056-000
462A023-25-0



TE Part #2160753002
55A0111-24-5



TE Part #CD31433001
FLHTC0311-0.50-2



TE Part #2-967640-1
4POS MQS REC COD B



TE Part #2358664-2
FLAP, ASSY, INLET COMBO 2, LEFT



TE Part #CAT-AQ6-CIC
DC Fast Charge CCS1 and CCS2 Inlet Kits



TE Part #2138622-1
RELAY, EVC135, 26 OHM COIL (15" WIRE)

Documents

Product Drawings
CHARGE INLET, COMBO 2, 90 DEGREE

English

CAD Files
3D PDF

3D



Customer View Model

[ENG_CVM_CVM_2375502-2_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2375502-2_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2375502-2_B.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HIVONEX CONNECTORS & CHARGING SOLUTIONS](#)

English

Product Specifications

[Application Specification](#)

English