

IEC contactor, TeSys Deca, nonreversing, 65A, 40HP at 480VAC, 3 phase, 3 pole, 3 NO, 24VAC 50/60Hz coil, open style

LC1D65A6B7

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys TeSys Deca	
Range of Product	TeSys Deca	
Product or Component Type	Contactor	
Device short name	LC1D	
Contactor application	Resistive load Motor control	
Utilisation category	AC-4 AC-1 AC-3 AC-3e	
Poles description	3P	
[Ue] rated operational voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC	
[le] rated operational current	80 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 65 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 65 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit	
[Uc] control circuit voltage	24 V AC 50/60 Hz	

Complementary

Motor power kW	11 kW at 400 V AC 50/60 Hz (AC-4) 18.5 kW at 220230 V AC 50/60 Hz (AC-3) 30 kW at 380400 V AC 50/60 Hz (AC-3) 37 kW at 500 V AC 50/60 Hz (AC-3) 37 kW at 660690 V AC 50/60 Hz (AC-3) 18.5 kW at 220230 V AC 50/60 Hz (AC-3e) 30 kW at 380400 V AC 50/60 Hz (AC-3e) 37 kW at 500 V AC 50/60 Hz (AC-3e) 37 kW at 660690 V AC 50/60 Hz (AC-3e)	
Maximum Horse Power Rating	40 hp at 460/480 V AC 50/60 Hz for 3 phase motors 5 hp at 115 V AC 50/60 Hz for 1 phase motors 10 hp at 230/240 V AC 50/60 Hz for 1 phase motors 20 hp at 200/208 V AC 50/60 Hz for 3 phase motors 20 hp at 230/240 V AC 50/60 Hz for 3 phase motors 50 hp at 575/600 V AC 50/60 Hz for 3 phase motors	
Compatibility code	LC1D	
Pole contact composition	3 NO	
Protective cover	With	
[Ith] conventional free air thermal current	10 A (at 140 °F (60 °C)) for signalling circuit 80 A (at 140 °F (60 °C)) for power circuit	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Irms rated making capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1 1000 A at 440 V for power circuit conforming to IEC 60947	
Rated breaking capacity	1000 A at 440 V for power circuit conforming to IEC 60947	
[lcw] rated short-time withstand	640 A 104 °F (40 °C) - 10 s for power circuit	
current	900 A 104 °F (40 °C) - 1 s for power circuit 110 A 104 °F (40 °C) - 10 min for power circuit	
	260 A 104 °F (40 °C) - 1 min for power circuit	
	100 A - 1 s for signalling circuit	
	120 A - 500 ms for signalling circuit	
	140 A - 100 ms for signalling circuit	
Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1	
	125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit	
Average impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit	
Power dissipation per pole	9.6 W AC-1 6.3 W AC-3	
	6.3 W AC-3e	
[Ui] rated insulation voltage	Power circuit 600 V CSA	
· · · · · · · · · · · · · · · · · ·	Power circuit 600 V UL	
	Signalling circuit 690 V IEC 60947-1	
	Signalling circuit 600 V CSA Signalling circuit 600 V UL	
	Power circuit 690 V IEC 60947-4-1	
Overvoltage category	III	
Pollution degree	3	
[Uimp] rated impulse withstand voltage	6 kV IEC 60947	
Safety reliability level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1	
Mechanical durability	6 Mcycles	
Electrical durability	1.4 Mcycles 80 A AC-1 <= 440 V	
-	1.45 Mcycles 65 A AC-3 <= 440 V	
	1.45 Mcycles 65 A AC-3e <= 440 V	
Control circuit type	AC 50/60 Hz	
Coil technology	Without built-in suppressor module	
Control circuit voltage limits	0.30.6 Uc (-40158 °F (-4070 °C)):drop-out AC 50/60 Hz	
	0.81.1 Uc (-40140 °F (-4060 °C)):operational AC 50 Hz	
	0.851.1 Uc (-40140 °F (-4060 °C)):operational AC 60 Hz 11.1 Uc (140158 °F (6070 °C)):operational AC 50/60 Hz	
Inrush power in VA	140 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 160 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))	
Hold-in power consumption in VA	13 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C))	
,	15 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))	
	45 W at 50/60 Hz	
Heat dissipation	45 W at 50/60 Hz	
	45 W at 50/60 Hz 419 ms opening	
·		
Operating time	419 ms opening	
Heat dissipation Operating time Maximum operating rate Connections - terminals	419 ms opening 1226 ms closing	
Operating time Maximum operating rate	419 ms opening 1226 ms closing 3600 cyc/h at 60 °C Control circuit: lugs-ring terminals - external diameter: 0.3 in (8 mm) Power circuit: lugs-ring terminals - external diameter: 0.6 in (16.5 mm) Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors flat Ø 6 mm	
Operating time Maximum operating rate Connections - terminals	419 ms opening 1226 ms closing 3600 cyc/h at 60 °C Control circuit: lugs-ring terminals - external diameter: 0.3 in (8 mm) Power circuit: lugs-ring terminals - external diameter: 0.6 in (16.5 mm) Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors flat Ø 6 mm M3.5	
Operating time Maximum operating rate Connections - terminals	419 ms opening 1226 ms closing 3600 cyc/h at 60 °C Control circuit: lugs-ring terminals - external diameter: 0.3 in (8 mm) Power circuit: lugs-ring terminals - external diameter: 0.6 in (16.5 mm) Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors flat Ø 6 mm	
Operating time Maximum operating rate Connections - terminals	419 ms opening 1226 ms closing 3600 cyc/h at 60 °C Control circuit: lugs-ring terminals - external diameter: 0.3 in (8 mm) Power circuit: lugs-ring terminals - external diameter: 0.6 in (16.5 mm) Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors flat Ø 6 mm M3.5 Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors Philips No 2 M3.5 Power circuit 53.1 lbf.in (6 N.m) EverLink BTR screw connectors hexagonal 0.4 in	
Operating time Maximum operating rate Connections - terminals	419 ms opening 1226 ms closing 3600 cyc/h at 60 °C Control circuit: lugs-ring terminals - external diameter: 0.3 in (8 mm) Power circuit: lugs-ring terminals - external diameter: 0.6 in (16.5 mm) Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors flat Ø 6 mm M3.5 Control circuit 15.05 lbf.in (1.7 N.m) EverLink BTR screw connectors Philips No 2 M3.5	

Auxiliary contact composition	1 NO + 1 NC	
Auxiliary contacts type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1	
Signalling circuit frequency	25400 Hz	
Minimum switching voltage	17 V for signalling circuit	
Minimum switching current	5 mA for signalling circuit	
Insulation resistance	> 10 MOhm for signalling circuit	
Non-overlap time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail Plate	

Environment

Standards	EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 CSA C22.2 No 14 UL 60947-4-1 IEC 60335-2-40:Annex JJ UL 60335-2-40:Annex JJ IEC 60335-1:Clause 30.2	
Product Certifications	CCC UL CB Scheme CSA CE UKCA Marine EAC	
IP degree of protection	IP20 front face IEC 60529	
Protective treatment	THIEC 60068-2-30	
Climatic withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible ambient air temperature around the device	-40140 °F (-4060 °C) e 140158 °F (6070 °C) with derating	
Operating altitude	09842.52 ft (03000 m)	
Fire resistance	1562 °F (850 °C) IEC 60695-2-1	
Flame retardance	V1 conforming to UL 94	
Mechanical robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor closed 15 Gn for 11 ms) Shocks contactor open 10 Gn for 11 ms)	
Height	4.8 in (122 mm)	
Width	2.2 in (55 mm)	
Depth	4.7 in (120 mm)	
Product Weight	1.90 lb(US) (0.86 kg)	

Ordering and shipping details

Category	US10I1222357
Discount Schedule	0112
GTIN	3389118328686

Returnability	Yes	
Country of origin	ID	

Packing Units

r adming dimes		
Unit Type of Package 1	PCE	
Nbr. of units in pkg.	1	
Package 1 Height	2.36 in (6.000 cm)	
Package 1 Width	5.51 in (14.000 cm)	
Package 1 Length	5.91 in (15.000 cm)	
Package weight(Lbs)	29.982 oz (850.000 g)	
Unit Type of Package 2	S02	
Number of Units in Package 2	10	
Package 2 Height	5.91 in (15.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	19.313 lb(US) (8.760 kg)	
Unit Type of Package 3	P06	
Number of Units in Package 3	160	
Package 3 Height	29.53 in (75.000 cm)	
Package 3 Width	31.50 in (80.000 cm)	
Package 3 Length	23.62 in (60.000 cm)	
Package 3 Weight	326.637 lb(US) (148.160 kg)	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	84
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Technical Illustration

Assembly's dimensions

