



Timing Relay, Type JCK, plug In, multifunction, programmable, 0.5 second to 999 hours, 10A, 240 VAC, 240 VAC 50/60 Hz

9050JCK70V24

Product availability: Stock - Normally stocked in distribution facility

Main

product range	9050JCK
product type	Timer
timing mode	Off-delay Trigger on-delay One shot falling edge One shot On-delay and off-delay Watchdog On-delay Repeat cycle Interval
timing range	0.199.9 min 0.059.99 s 1999 s 0.199.9 h 0.199.9 s 1999 h
supply voltage	240 V AC

Complementary

power consumption	3.2 VA
current rating	10 A
switch function	DPDT
contact composition	2 NO + 2 NC
contact material	Silver nickel
maximum switching voltage	240 V AC
mounting type	Socket
number of pins	11
shape of pins	Tubular
for use with	8501NR61 8501NR62

Environment

certifications	UL Listed UL Recognized CE
ambient temperature range - operational	-2850 °C (-18122 °F)
Height	2 4 in (60 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	1.7 in (44 mm)
Depth	3.6 in (91 mm)

Ordering and shipping details

Category	US10CP221652
Discount Schedule	0CP2
GTIN	785901132707
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	1.90 in (4.826 cm)
Package 1 Length	4.30 in (10.922 cm)
Package weight(Lbs)	5.280 oz (149.685 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	4.50 in (11.43 cm)
Package 2 Width	10.00 in (25.4 cm)
Package 2 Length	11.00 in (27.94 cm)
Package 2 Weight	3.0005 lb(US) (1.361 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	50	

Use Better


Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture		
Take-back	No	


Dimensions Drawings

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams



(1) Do not apply DC voltage to the 240 Vac timers (voltage code V24).