

Product data sheet

Specifications



Multisound siren, prewired,
Harmony XVS, white colour, 0...105
dB, 43 tones, 120V AC

XVS14GMW

Main

Range of product	Harmony XVS
Product or component type	Multisound siren
Device short name	XVS

Complementary

Colour	White
Material	PC (polycarbonate): back cover PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): front PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): back
Product weight	1.2 kg
Marking	CE
Mounting support	Bracket
fixing mode	3 holes Ø 9 mm
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	100 mA at 120 V
Electrical connection	Cable: 6.5...8.5 mm, 0.33 mm ² / AWG 22 (signalling circuit) Cable: 6.5...8.5 mm, 0.52 mm ² / AWG 20 (power circuit)
Width	140 mm
Height	114 mm
Depth	223 mm

Environment

Signalling type	43 tones siren
Standards	IEC 61000-6-2 IEC 61000-6-3 IEC 60947 EN 60947-5
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP53 conforming to IEC 60529
[Us] rated supply voltage	120 V AC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Noise level	0...105 dB (continuous or intermittent tone) at 1 m
-------------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.49 cm
Package 1 Width	16 cm
Package 1 Length	27.94 cm
Package 1 Weight	1.56 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.856 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	24
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	24 cm
Package 3 Weight	38.064 kg

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Fe0ee3ab-dd49-4abe-bd8e-c49754e2c442
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No

Dimensions Drawings

Siren

Dimensions



Technical Illustration

Dimensions

