



Terminals & Splices > Splices



Sealable: **Yes**

Compatible Insulation Diameter Range: **1.9 mm [.075 in]**

Wire Size: **350 – 2000 CMA**

Primary Product Color: **Clear**

Product Length: **29.7 mm [1.17 in]**

Features

Product Type Features

Sealable	Yes
----------	-----

Body Features

Product Weight	1 g
Insulation Material	Heat Shrink Radiation-Crosslinked Modified Polyvinylidene Fluoride
Primary Product Color	Clear

Contact Features

Barrel Type	Open
-------------	------

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Dimensions

Compatible Insulation Diameter Range	1.9 mm[.075 in]
Wire Size	350 – 2000 CMA
Product Length	29.7 mm[1.17 in]

Usage Conditions

Fluid Resistance	Immersion
Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]



Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG8162-000
[HL1920E-230V-EURO](#)

Customers Also Bought



TE Part #NB08916001
[ATUM-12/3-0-40MM](#)



TE Part #D369-R33-AS0
[369 3 WAY REC, NO CONTACTS, SKT](#)




TE Part #CH17364001
[RNF-3000-18/6-2-FSP](#)



TE Part #CAT-HST-RNF100-0
[RNF-100-0 Heat Shrink Tubing](#)



TE Part #L000601-80
[UWB Ceramic chip Ant with EVB assy](#)



TE Part #323196
[TERMINAL,SOLIS FLAG R 6 10](#)



TE Part #1752680-7
[HYP10 SOLIS FLAG 6AWG NEST](#)



TE Part #1752681-3
[HYP10 SOLIS FLAG 6-2AWG INDENTER](#)



TE Part #2405869-8
[CT 8P 300MM CABLE ASSEMBLY 2-179228-8](#)

Documents

Product Drawings

[D-1744-01](#)

English

Datasheets & Catalog Pages

[Harness Repair Products Quick Reference Guide](#)

English

Product Specifications

[Product Specification](#)



English

Installation Procedure for Products Designed for In-Line Splice Installed with Hot Air Gun

English