



Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Caps



Wall Type: **Single Wall**
Material Code: **3**
Material Systems Code: **10**
Adhesive Requirement: **Adhesive Purchased Separately**
Operating Temperature Range: **-55 – 135 °C [-67 – 275 °F]**

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Configuration Features

Adhesive Requirement	Adhesive Purchased Separately
----------------------	-------------------------------

Body Features

Shrink Ratio	2:1
Primary Product Color	Black
Flexibility	Flexible
Primary Product Material	Crosslinked Polyolefin
Sealant Type	None
Material Code	3
Material Systems Code	10

Dimensions

Recovered Wall Thickness (Nominal)	1.02 mm[.04 in]
Product Length	22 mm[.876 in]
Wall Thickness	Medium
Recovered Inside Diameter (Max)	2 mm[.08 in]
Expanded Inside Diameter (Min)	5.1 mm[.2 in]

Usage Conditions

--	--



Flammability Performance	Flame-Retardant
Resistance Properties	Immersion Protection
Resistance Protection	Suitable for occasional exposure to fluids
Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]

Other

Molded Part Shape Code	101A
Size Code	11

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # D856933001
100G1121-3.00-0/9-0



TE Part # CD68003001
100G1131-3.00-2/6/9-0



TE Part # 2630093001
100G0111-4.00-45




TE Part # D292083001
100G0111-3.00-1



TE Part # CQ56513001
100G0121-3.00-0/9



TE Part # E221163001
100G0111-4.00-8



TE Part # 890060-000
S1017-1.0X50



TE Part # CQ91273001
100G1121-3.00-6/9-0



TE Part # CD25293001
ZHPCG-15-1.0-0



TE Part # F807323001
ZHPCG-35-4.0-0



TE Part # E267123001
100G0111-4.00-1



TE Part # CQ47163001
100G0111-3.00-5



TE Part # CT89333001
ZHPCG-36-2.5-0



TE Part # CT88833001
100G0111-3.00-3



TE Part # C016423001
ZHPCG-35-1.5-0



TE Part # CT86523001
ZHPCG-15-4.0-2



TE Part # CQ64993001
100G1121-4.00-6/9-0



TE Part # 2584333002
100G0111-4.00-6




TE Part # 8089383001
ZHPCG-35-6.0-0



TE Part # CQ48473001
ZHPCG-35-6.0-2

Customers Also Bought



 TE Part #L9000111-01 Antenna Dome 2.4GHz 1.32 216 UFL	 TE Part #0915756003 LSTT-R-9.5-0	 TE Part #CAT-HST-RNF3000 RNF-3000 Heat Shrink Tubing	 TE Part #9692653001 TR16-95-0
 TE Part #2-34141-1 PG R 22-16 COMM 22-18 MIL 4	 TE Part #324599 TERMINAL,BUDG SPD FLG 26-22 2	 TE Part #1423673-7 W51-A121B1-20=CKTBKR,THERM,ROC	 TE Part #A63971-000 101A031-3-05-0
 TE Part #GA10K3CG1267 CHPC-TAIWAN GOLD CHIP			

Documents

Product Drawings
101A011-3-0

English

Datasheets & Catalog Pages
1654025_Sec4_101A011to094

English

1654025_Sec4_-3

English

Raychem Molded Parts Visual Guide
English