



### Overview

Presentation	Battery cabinet that includes Lithium-ion batteries, Battery Management System (BMS), switchgear, power supply, and communication interface.
Lead time	Special Order - Call for Quoted Lead Times

### Main

Battery Type	Li-Ion (Lithium Ion)
Provided Equipment	Installation guide

### Physical

Color	White
Height	77.56 in (197 cm)
Width	25.59 in (65 cm)
Depth	23.11 in (58.7 cm)
Net Weight	1036.17 lb(US) (470 kg)
Surface Finish	Powder coated

### Output

Battery Capacity	67 Ah
------------------	-------

### Conformance

Standards	UL 9540A
-----------	----------

### Environmental

Ambient Air Temperature for Operation	64...82 °F (18...28 °C)
Operating altitude	0...9842.52 ft (0...3000 m)
Ambient Air Temperature for Storage	32...104 °F (0...40 °C)

### Batteries & Runtime

Battery Placement	Battery Cabinet
Battery manufacturer	Samsung
Device mounting	Enclosed battery cabinet

### Ordering and shipping details

GTIN	731304426141
Package weight(Lbs)	1064.83 lb(US) (483 kg)

## Packing Units

Package 1 Height	84.65 in (2150 mm)
Package 1 width	47.24 in (1200 mm)
Package 1 Length	31.50 in (800 mm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Tetrabromobisphenol A, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------