



TE Internal #: AEA139N00000201000

Cable-to-Panel, Circular Connector Receptacle, 17 Position, Shell Size 23, Signal, Panel Mount, Electrodeposited Nickel, Zinc Alloy, PBT GF

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Panel**

Connector Mounting Type: **Panel Mount**

Number of Positions: **17**

Sealable: **No**

Circuit Application: **Signal**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Panel
Sealable	No
Circular Connector Type	Circular Connector Receptacle
Shell Type	Metal

Configuration Features

Number of Positions	17
Number of Signal Positions	17

Electrical Characteristics

Operating Voltage	125 VDC
-------------------	---------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy



Circular Connector Insulation Material Type

PBT GF

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
Mating Retention Type	Screw
Connector Mounting Type	Panel Mount

Housing Features

Circular Connector Shell Size	23
Alignment Keyed	0°

Usage Conditions

Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these




limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # T623PT217P0-011
M23-SPT17-PC-D8.5-NI




TE Part # T623PT217P0-013
M23-SPT17-PC-D14.3-NI




TE Part # ASA623N00390235000
623 PLUG




TE Part # ASA014N00400235000
623 PLUG



TE Part # T623PT217P0-012
M23-SPT17-PC-D10.0-NI



TE Part # ASB014N00410216000
623 PLUG



TE Part # ASA014N00610235000
623 PLUG

TE Part # C0-0235-000-P00
DIGITAL CRIMPING TOOL, SMALL

TE Part # C0-0101-000-P00
CRIMPING TOOL SMALL WITH POSITIONER

Customers Also Bought



TE Part #61-0004-011-P00
CONTACT PIN 1 MM



TE Part #BGC106N00001216000
923 RECEPTACLE, ANGLED, ROTATABLE



TE Part #AEA110N00000201000
623 RECEPTACLE, SPEEDTEC-READY



TE Part #AGC110N00001215000
623 RECEPTACLE ANGLED ROTATABLE





TE Part #BGC110N00001216000
923 RECEPTACLE, ANGLED, ROTATABLE



TE Part #CSA263N00440001000
940 PLUG



TE Part #AGC139N00001215000
623 RECEPTACLE ANGLED ROTATABLE



TE Part #BGC110N00001116000
923 RECEPTACLE, ANGLED, ROTATABLE

TE Part #40-0948-000-P00
623 INSULATION INSERT, 17-PIN

TE Part #N2-0111-000-P00
623 CODING SLEEVE

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_AEA139N00000201000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_AEA139N00000201000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_AEA139N00000201000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

AEA139N00000201000

English

fuer Datenblaetter, die online konfigurierbar sind

German

Product Specifications

German