



WV

TE Internal #: F51616-000

White, Industrial Label, Die-Cut, High Tack Permanent Acrylic Adhesive, 38.1 mm [1.5 in] Width, 19.1 mm [.75 in] Height, WV, Standard Labels

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > WV High Tack White Vinyl Labels



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Permanent Acrylic Adhesive**

Product Width: **38.1 mm [1.5 in]**

Length of Label Roll: **55.5 m [182.08 ft]**

[All WV High Tack White Vinyl Labels \(25\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	White
Primary Product Material	Vinyl Film

Dimensions

Product Width	38.1 mm[1.5 in]
Product Height	19.1 mm[.75 in]

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Printer/Label Features

Number of Labels Across	2
Label Style	Die-Cut
Length of Label Roll	55.5 m[182.08 ft]
Label Thickness	75 Micron

Packaging Features

--	--



Packaging Method	Roll
Packaging Quantity	5000

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186500-1
T3212-PRINTER



Also in the Series | WV

Standard Labels(7)

Customers Also Bought

TE Part #91501-1
CCII MICRO MNL REC 24-20 ASSY

TE Part #170365-3
MINI UNIVERSAL M-N-L SOCKET LPTE Part #170366-3
MINI UNIVERSAL M-N-L SOCKET LPTE Part #350690-3
UMNL PIN 24-18 PTPPHBZ L/PTE Part #1-480708-0
12P UMNL PLUG HSG NATLTE Part #2-520103-2
ULTRA-FAST 250 ASSEMBLY TAB 22-18 AWG BRTE Part #640713-1
02P UMNL STR/REL & INSERTTE Part #794616-6
FREE HANG DBL ROW HSG 6 POSTE Part #2-794617-0
20POS,MICRO MNL,RCPT HSGTE Part #1445730-1
STRN RELIEF ASY,STRT SIZE 8

Documents

Product Drawings

WV-381191-5-9

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

WV-381191-5-9

White, Industrial Label, Die-Cut, High Tack Permanent Acrylic Adhesive, 38.1 mm [1.5 in] Width, 19.1 mm [.75 in] Height, WV, Standard Labels



EET V-9

English

Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English