


TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.25 .XX ±0.13


.XXX ±0.10

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER 1 ORIGINAL PANEL CUT-OUT ADDED APRIL 2024 (2)






## RECOMMENDED PANEL CUT-OUT



DIM' TOLERANCE = ±0.05

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.



PANEL THICKNESS

NOTES:

MATERIAL:

**HOUSING:** PA6T, UL94V-0

SHELL: STEEL, NICKEL PLATED

CONTACT: PRECISION MACHINED COPPER ALLOY,

**GOLD FLASH PLATED** 

**OPERATING TEMPERATURE:** -25°C TO 85°C

**CURRENT RATING: 5A PER CONTACT** 

**CONTACT RESISTANCE:**  $10m\Omega$  MAX. **INSULATOR RESISTANCE:** 5000MΩ min.

**DIELECTRIC** 

WITHSTANDING VOLTAGE: 1000V AC rms

## 629W SERIES D-SUB CONNECTOR



**EDAC INC** TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

SCALE: 1:1	SHEET 1 OF 1
CHECKED:	DATE:
DRAWN: C.B	DATE: AUG. 01/2018
SW REFERENCE NO.:	629W ASSEMBLY

**ISSUE** DRAWING NUMBER: 629-W25-240-012 PART NUMBER: 629-W25-240-012

2