

Die cast empty control station, Harmony XAP, XB2 SL, zinc alloy, grey, M20, undrilled, 80x80x51,5mm, UL cULus

XAPD11

# Main

| Range of product              | Harmony XAP  |  |  |  |  |  |
|-------------------------------|--|--|--|--|--|--|
| Product or component type     | Die-cast empty control station   |  |  |  |  |  |
| Device short name             | XAPD   |  |  |  |  |  |
| Product destination           | For Ø 22 mm control and signalling units   |  |  |  |  |  |
| Product front plate size      | 80 x 80 mm   |  |  |  |  |  |
| Usable depth                  | 49 mm  |  |  |  |  |  |
| Number of cut-out             | Without cut-out  |  |  |  |  |  |
| Colour of base of enclosure   | Grey (RAL 7035)  |  |  |  |  |  |
| Colour of cover               | Grey (RAL 7035)  |  |  |  |  |  |
| Material                      | Die cast zinc  |  |  |  |  |  |
| Sale per indivisible quantity | 1  |  |  |  |  |  |
| IP degree of protection       | IP65 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 IP66 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 IP69 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 |  |  |  |  |  |

# Complementary

| Number of vertical rows   | 0                                 |  |  |  |  |  |
|---------------------------|-----------------------------------|--|--|--|--|--|
| Number of horizontal rows | 0                                 |  |  |  |  |  |
| Control station type      | Metal                             |  |  |  |  |  |
| Cable entry               | 2 x cable gland conforming to ISO |  |  |  |  |  |
| Thread type               | M20 x 1.5                         |  |  |  |  |  |
| CAD overall width         | 80 mm                             |  |  |  |  |  |
| CAD overall height        | 80 mm                             |  |  |  |  |  |
| CAD overall depth         | 51.5 mm                           |  |  |  |  |  |
| Net weight                | 0.455 kg                          |  |  |  |  |  |

# **Environment**

| Protective treatment                  | тс                              |
|---------------------------------------|---------------------------------|
| Ambient air temperature for storage   | -4070 °C                        |
| Ambient air temperature for operation | -2570 °C                        |
| Electrical shock protection class     | Class I conforming to IEC 61140 |
| Degree of protection                  | UL type 4 conforming to UL 50 E |

| IK degree of protection       | IK07 conforming to IEC 62262                 |
|-------------------------------|--|
| Resistance to chemical agents | Special treatment can be obtained on request |
| Product certifications        | UL<br>cULus<br>EAC                           |

# **Packing Units**

| PCE        |
|------------|
| 1          |
| 8.000 cm   |
| 8.500 cm   |
| 9.000 cm   |
| 550.000 g  |
| S02        |
| 12         |
| 15.000 cm  |
| 30.000 cm  |
| 40.000 cm  |
| 6.844 kg   |
| P06        |
| 192        |
| 75.000 cm  |
| 80.000 cm  |
| 60.000 cm  |
| 117.504 kg |
|            |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

| <b>⊘</b> Environmental footprint |                               |
|----------------------------------|-------------------------------|
| Total lifecycle Carbon footprint | 3                             |
| Environmental Disclosure         | Product Environmental Profile |

#### **Use Better**


| Materials and Substances               |   |
|--|---|
| Packaging made with recycled cardboard | Yes   |
| Packaging without single use plastic   | Yes   |
| EU RoHS Directive                      | Pro-active compliance (Product out of EU RoHS legal scope)  |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

#### **Use Again**

| ○ Repack and remanufacture      |  |  |  |  |  |  |  |
|---------------------------------|--|--|--|--|--|--|--|
| End of life manual availability | No need of specific recycling operations |  |  |  |  |  |  |
| Take-back                       | No                                       |  |  |  |  |  |  |

# **Dimensions Drawings**

#### **Dimensions and Fixing**



(1) : 1 hole, with blanking plug (protrusion 6 mm/0.24 in.), for cable gland ISO M20 x 1.5

(2): 1 hole, without blanking plug, for cable gland ISO M20 x 1.5

(3): 2 x Ø 5.6 mm/0.22 in. holes, depth 19 mm/0.75 in.

P: Usable depth

| a b |      | С  |      | G    |      | Н  |      | P . |      |    |      |
|-----|------|----|------|------|------|----|------|-----|------|----|------|
| mm  | in.  | mm | in.  | mm   | in.  | mm | in.  | mm  | in.  | mm | in.  |
| 80  | 3.15 | 80 | 3.15 | 51.5 | 2.03 | 50 | 1.97 | 65  | 2.56 | 49 | 1.93 |

Image of product / Alternate images

# **Alternative**



