

Product data sheet

Specifications



PanelSeT CRN plain door w/o
mount.plate. H500xW400xD200
IP66 IK10 RAL7035..

NSYCRN54200

Main

Range	PanelSeT
Product name	PanelSeT CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	500 mm
Enclosure nominal width	400 mm
Enclosure nominal depth	200 mm
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door 1 lock
Door type	Plain
Mounting plate description	Without mounting plate

Complementary

body type	Back welded with double profile forming a protected sealed area Sides made from a single folded section
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body: steel
Surface finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL CUL
Product certifications	cUL UL DNV-GL
Product weight	8.382 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	51.500 cm
Package 1 Width	21.000 cm
Package 1 Length	41.000 cm
Package 1 Weight	8.382 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	40
Package 2 Height	198.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	348.000 kg

Contractual warranty

Coverage	Core product
Warranty	18 months

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	79
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features



Sturdy components' protection



Earthing studs included



Large choice of dimensions & accessories



Quality & aesthetics



Easy to equip
Easy to maintain



Built to last

