

836 Pen



No-Clean, Lead-Free Flux

836-P is a solder flux pen containing a halogenfree organic flux with low activity. The flux has a low solids content and leaves virtually no residue. Solder joints appear shiny after soldering, even without cleaning.

This no-clean flux pen is designed for the prototyping, rework and repair of conventional and surface mount circuit boards



Features & Benefits

Meets IPC J-STD-004B and type ORLO

For both leaded and lead-free solders

Chiseled tip allows precise application

Residues do not require cleaning

Halogen-free

RoHS compliant

Easy application

Non-corrosive and non-conductive residue

Storage and Handling

Store between 18 and 27 °C in a dry area, away from sunlight (see SDS).

Properties

Color	Colorless	Visual
Solids %	1.9–2.5%	—
Density	0.8 g/mL	—
Flux Classification	ORLO	J-STD-004B, MIL-F-14256F
Flux Type	Organic	J-STD-004B
Flux Activity	Low	J-STD-004B
Copper Mirror	Pass	IPC-TM-650 2.3.32
Cleaning Requirements	Recommended	—
Halides (by weight)	<0.5%	J-STD-004B
Surface Insulation Resistance (SIR)	$2.1 \times 10^9 \Omega$	IPC-TM-650 2.6.3.3
Acid Number (mg KOH/g)	14–16	Titration
Shelf Life	5 y	—

Available Packaging

Part #	Packaging	Net Vol.	Net Wt.
836-P	Pen	10 mL	8.10 g
836-PCA	Pen	10 mL	8.10 g

Application Instructions

Read the product SDS for more detailed instructions before using this product.

1. Depress the tip against a hard surface until the felt tip gets wet, but not flooding.
2. Gently brush the wet tip onto the soldering area to apply. To keep the tip saturated and control the flow, only press in the tip as needed.
3. Clean residue with MG #4140 or #413B flux removers.

Disclaimer: This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

MG Chemicals 1210 Corporate Drive Burlington, Ontario, Canada L7L 5R6 ISO 9001:2015 Quality Management System SAI Global File: 004008
support@mgchemicals.com **North America** +(1) 800-340-0772 **International** +(1) 905-331-1396 **Europe** +44 1663 362888 **23 September 2025 / Ver. 3.0**