

ClimaSys PTC heating resistance 150W,110-250V

NSYCR150WU2

Overview

Lead time Usually Ships within 4 Weeks

Main

Range	ClimaSys	
Product name	ClimaSys CR	
Product or component type	Resistance heater	
Power range	150 W	
Input voltage	110250 V AC 50/60 Hz	

Complementary

Operating position	Vertical	
Ambient air temperature for operation	-4070 °C	
IP degree of protection	IP20	
Product certifications	VDE UL	
Material	Body: extruded aluminium	
Height	285 mm	
Width	80 mm	
Depth	70 mm	
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed	
fixing mode	By clips	
Mounting support	35 mm DIN rail	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	8.000 cm
Package 1 Length	28.500 cm
Package 1 Weight	805.000 g
Unit Type of Package 2	CAR

Number of Units in Package 2	12
Package 2 Height	15.500 cm
Package 2 Width	26.000 cm
Package 2 Length	58.000 cm
Package 2 Weight	10.560 kg
Unit Type of Package 3	P12
Number of Units in Package 3	360
Package 3 Height	120.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	330.000 kg

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	60bb7229-9ac3-41cb-896e-a93aa448ebf8
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins