

Customer Specification

PART NO. 74006

Construction

						Diameter ("in")	
1) Component 1						4 x 1 PAIR	
a) Conductor						26 (19/38) AWG Bare Copper	0.020
b) Insulation						0.010" Wall, Nom. Polypropylene (PP)	0.040
(1) Color(s)							
Pair	Color	Pair	Color	Pair	Color		
1	WHITE/BLUE - BLUE	3	WHITE/GREEN - GREEN				
2	WHITE/ORANGE - ORANGE	4	WHITE/BROWN - BROWN				
c) Pair						2/Cond Cabled Together	
(1) Twists						Staggered Lays	
2) Cable Assembly						4 Components Cabled	
a) Twists						5.3 Twists/ft. min.	
3) Shield						Alum/Mylar Tape, 25% Overlap (min.)	
a) Foil Direction						Foil Facing Out	
b) Braid						Tinned Copper, 80% Coverage (min.)	
4) Jacket						0.031" Wall, Nom., TPU (ZH)	0.252 (0.266 max.)
a) Color(s)						BLACK	
b) Jacket Separator						Nonwoven Polyester Tape, 25% Overlap, Min.	
c) Print						ALPHA WIRE-* P/N 74006 4PR 26 AWG INDUSTRIAL ETHERNET SHIELDED ANSI/TIA-568-C.2 CAT5E VERIFIED CE ROHS (SEQ FOOTAGE) * = Factory Code	

Applicable Specifications

Physical & Mechanical Properties				
1) Temperature Range		-40 to 80°C(static), -5 to 50°C (dynamic)		
2) Bend Radius		5X Cable Diameter (static), 10X Cable Diameter (dynamic)		
3) Pull Tension		18 lbs. max.		
4) Continuous Flex		2 million cycles		
5) Torsional Flex		1 million cycles		
Electrical Properties		Engineering purposes only		
1) Max. operating voltage UL		300 V _{RMS}		
2) Dielectric strength cond. – cond. (2 sec.)		2.5kVdc		
3) D.C. resistance conductor		< 140 ω/km		
4) Resistance unbalance		< 2%		
5) D.C. insulation resistance		> 5000 Mω.km		
6) Mutual capacitance		< 56 nF/km		
7) Capacitance unbalance		< 1600 pF/km		
8) Velocity of propagation @ 4 - 100MHz		≥ 60%		
9) Skew @ 1 - 100 MHz		≤ 40 ns/100m		
10) Propagation delay @ 1 - 100 MHz		≤ 534 + 36/√f ns/100m		
11) Mean characteristic impedance (Zcm) @ 100 MHz		100 ± 15 ω		
12) Input impedance 4 - 100MHz		100 ± 15 ω		
Frequency(MHz)	Max. Attenuation(dB/100m)	Min. NEXT(dB)	Min. PS-NEXT(dB)	Min. ELFEXT(dB/100m)
1	3.2	65	62	64
4	6.2	56	53	52
10	9.5	50	47	44
16	12.1	47	44	40
31.25	17.9	43	40	34
62.5	24.8	38	35	28
100	32.0	35	32	24

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 500 FT	12 x 6 x 3.5 Continuous Length
	Spool dimensions may vary slightly.

www.alphawire.com

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374

Tel: 1-800-52 ALPHA

Although Alpha Wire (“Alpha”) makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 74006

74006, RoHS-Compliant Commencing With 9/30/2013 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above, including all packaging materials, is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with UK - RoHS. The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014. This product is also in compliance with China RoHS 2 per GB/T 26572-2011.

Substance

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) , Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering 6/16/2025

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374
Tel: 1-908-925-8000