



Main

Range	Vigilohm
Device short name	Cardew C
Product or Component Type	Surge limiter
Range compatibility	Vigilohm

Complementary

Rated voltage	1000 V
Network rated voltage	1000...1560 V - AC neutral distributed) 660...1000 V - AC neutral not distributed)
[Ui] rated insulation voltage	1600...2400 V AC
Breaking capacity	40 kA AC 50 Hz for 0.2 s
Product Weight	2.20 lb(US) (1 kg)
Width	2.76 in (70 mm)
Height	6.30 in (160 mm)
Depth	3.94 in (100 mm)

Environment

Standards	NF C 15-100 NF C 63-150
Ambient Air Temperature for Operation	23...104 °F (-5...40 °C)
Ambient Air Temperature for Storage	-13...158 °F (-25...70 °C)

Ordering and shipping details

GTIN	3303430501831
Nbr. of units in pkg.	1
Package weight(Lbs)	24.34 oz (690 g)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.94 in (10 cm)
Package 1 width	4.53 in (11.5 cm)
Package 1 Length	6.69 in (17 cm)
Unit Type of Package 2	S04
Number of Units in Package 2	16
Package 2 Weight	25.79 lb(US) (11.7 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)

Offer Sustainability

EU RoHS Directive	Not compliant
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------