

Light module, light block, Harmony 9001K, Harmony 9001SK, Harmony 9001SK, 30mm, LED red, 24...28V

9001KM35LR

Main

Range of product	Harmony 9001K Harmony 9001SK	
Product or component type	Light module Light block	
Device short name	9001K	
Bulb base	BA 9s	
Light block supply	Direct via integral resistance 0.28 VA	

Complementary

Light source	LED (bulb included)	
Light block colour	Red	
[Us] rated supply voltage	2428 V AC at 5060 Hz	

Environment

Protective treatment	TC	
Ambient air temperature for storage	-4070 °C -40158 °F	
Ambient air temperature for operation	-2570 °C -13158 °F	
IP degree of protection	IP20 conforming to IEC 60529	
Standards	UL 508 CSA C22.2 No 14 EN/IEC 60947-5-4 EN/IEC 60947-5-1 EN/IEC 60947-1 JIS C 4520 JIS C 852	
Product certifications	UL listed CSA NEMA	
Electrical shock protection class	Class II conforming to IEC 61140	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn conforming to IEC 60068-2-27	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	5.1 cm	
Package 1 Width	5.8 cm	
Package 1 Length	9.5 cm	
Package 1 Weight	72.6 g	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances		
Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d	
REACh Regulation	REACh Declaration	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.	

Use Again

○ Repack and remanufacture		
Take-back	No	