


Product data sheet

Specifications



Terminal block Linergy TR, push-in type, basic disconnect terminal, 2 points, 2.5mm², grey, set of 50

NSYTRP22TB

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Linergy
Product name	Linergy TR
Product or Component Type	Terminal block
Device short name	TRP
Terminal block type	Removable carrier disconnect
Associated connection component	Diode Cylindrical fuse Blade
Terminal block level	1
Mounting Mode	Clip-on
Nominal cross section	0.004 in ² (2.5 mm ²)
Length	2.4 in (62 mm)
color	Gray
Quantity per Set	Set of 50

Complementary

Fuse size	5 x 20 mm 6 x 32 mm
Width	0.2 in (5.2 mm)
Height	1.4 in (36.5 mm)
Connections - terminals	1 x push-in upstream 1 x push-in downstream
number of connections	2
Connection position	Top
Number of measurement input	2
Cable cross section	0.0002...0.004 in ² (0.14...2.5 mm ²), flexible without cable end 0.0002...0.006 in ² (0.14...4 mm ²), solid
Wire stripping length	0.4 in (10 mm)
Tool type	Disconnection flat screwdriver Connection without tool
[Ue] rated operational voltage	400 V EN/IEC 60947-7-1 300 V UL 300 V CSA
Line Rated Current	20 A EN/IEC 60947-7-1 20 A UL 20 A CSA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Material	Polyamide 6/6: insulating case
Dielectric loss	0.01 at 1 MHz IEC 60250 0.01 at 1 MHz VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m IEC 60093 10000 MΩ.m VDE 0303-T30
Surface resistance	1000 GΩ IEC 60093 1000 GΩ VDE 0303-T30
Creep resistance	500 CTI (> 400 kB) IEC 60093 500 CTI (> 400 kB) VDE 0303-T30
Flame retardance	V0 0.03 in (0.8 mm) UL 94
Product Weight	0.3 oz (8 g)
Range compatibility	PrismaSeT G PrismaSeT P PrismaSet HD PrismaSeT Pack 250 PanelSeT Mureva TeSys
Product Compatibility	Spacial enclosures

Environment

Product Certifications	UL VDE CSA GL
Dielectric strength	1000 V IEC 60243-1
Ambient air temperature for operation	-40...266 °F (-40...130 °C) IEC 60216-1 -40...266 °F (-40...130 °C) VDE 0304-T21

Ordering and shipping details

Category	US10CP521715
Discount Schedule	0CP5
GTIN	3606480533389
Returnability	Yes
Country of origin	PL

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.20 in (0.500 cm)
Package 1 Width	1.57 in (4.000 cm)
Package 1 Length	2.56 in (6.500 cm)
Package weight(Lbs)	0.247 oz (7.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	1.77 in (4.500 cm)
Package 2 Width	2.76 in (7.000 cm)

Package 2 Length	10.63 in (27.000 cm)
Package 2 Weight	13.651 oz (387.000 g)
Unit Type of Package 3	S03
Number of Units in Package 3	1250
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	22.170 lb(US) (10.056 kg)



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	5
--	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
--	-----

Packaging without single use plastic	Yes
--------------------------------------	-----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Halogen content performance	Halogen free plastic parts product
-----------------------------	------------------------------------

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
---------------------	--

Take-back	No
-----------	----