

# Product data sheet

Specifications



## surge arrester, Multi9 PRD1 75r, 3P, 120/208 V

M9L13208

### Main

Range	Multi9
Product name	Multi9 PRD1
Product or component type	Surge arrester
Device short name	PRD1 75r
Poles description	3P
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Standards	UL 1449:ed. 4

### Complementary

Surge arrester class type	Type 1
Surge arrester technology	MOV
Wiring configuration	4-wire
Nominal discharge current	Common mode: 20 kA (L/PE)
Maximum discharge current	75 kA
[Iimp] impulse current	75 kA
[Uc] maximum continuous operating voltage	Common mode: 175 V AC L/N Differential mode: 350 V AC L/L
Maximum [Up] voltage protection level	<600 V L/N <1200 V L/L
Disconnector device type	Associated circuit breaker 30 A curve C 10 kA
Short-circuit withstand	200 kA
Local signalling	Green mechanical indicator for operating Red mechanical indicator for end of life
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	6
Height	91.7 mm
Width	52.5 mm
Depth	71.4 mm
Product weight	522 g
Colour	Grey (RAL 7035)

<b>Response time</b>	< 25 ns
<b>Connections - terminals</b>	Tunnel type terminal 6...35 mm <sup>2</sup> (AWG 10...AWG 2) - rigid Tunnel type terminal 6...25 mm <sup>2</sup> (AWG 10...AWG 4) - flexible Tunnel type terminal (dry contacts) 0.5...1.5 mm <sup>2</sup>
<b>Wire stripping length</b>	10 mm for L/N connection 10 mm for PE connection 6 mm for dry contacts connection
<b>Tightening torque</b>	3 N.m L/N 3 N.m PE

## Environment

<b>IP degree of protection</b>	NEMA 1 built-in:
<b>Pollution degree</b>	3
<b>Relative humidity</b>	0...95 %
<b>Operating altitude</b>	2000 m
<b>Ambient air temperature for operation</b>	-25...60 °C
<b>Ambient air temperature for storage</b>	-40...85 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	6.5 cm
<b>Package 1 Width</b>	9.2 cm
<b>Package 1 Length</b>	12.2 cm
<b>Package 1 Weight</b>	397.0 g
<b>Unit Type of Package 2</b>	S02
<b>Number of Units in Package 2</b>	16
<b>Package 2 Height</b>	15.0 cm
<b>Package 2 Width</b>	30.0 cm
<b>Package 2 Length</b>	40.0 cm
<b>Package 2 Weight</b>	6.694 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant
SCIP Number	A9614fa2-07f8-47d1-a2fe-e27b32003d8d
REACH Regulation	<a href="#">REACH Declaration</a>
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Use Again

### Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins