

CSH2

APC Smart-UPS Charge Mobile Battery for Microsoft Surface Hub 2



Overview

Presentation	APC™ Smart-UPS Charge Mobile Battery is a lithium-ion battery system designed to power Microsoft Surface Hub 2 on-the-go for over 100 minutes, so you stay connected regardless of the location.
Lead time	Usually in Stock

Main

Main Input Voltage	100 V 120 V 230 V
Plug standard	IEC 60320 C13
Battery Type	Li-Ion (Lithium Ion)
Provided Equipment	DC Cable Detachable IEC C13 to IEC C14 power cord Screw set User Manual USB cable

Physical

Height	16.9 in (429.26 mm)
Width	11 in (279.40 mm)
Depth	3.5 in (88.90 mm)
Net Weight	22 lb(US) (9.98 kg)
Mounting Mode	Not rack-mountable
USB compatible	Yes

Input

Input Frequency	40 - 70 Hz
-----------------	------------

Conformance

Product Certifications	California (CEC) Battery Charger CE CTUVus UN 38.3
Standards	FCC Part 15 class A

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...85 %
Ambient Air Temperature for Storage	-4...140 °F (-20...60 °C)
Storage Relative Humidity	Non-condensing 0...95 %

Batteries & Runtime

Included Battery Modules	1
Battery Slots Empty	0

Ordering and shipping details

GTIN	731304402763
Package weight(Lbs)	28.66 lb(US) (13 kg)

Packing Units

Package 1 Height	16.9 in (429.26 mm)
Package 1 width	11 in (279.40 mm)
Package 1 Length	3.5 in (88.90 mm)
Number of Units in Package 3	8

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------