

Multisound siren, Harmony XVS, white colour, 106dB, 2tones, 230V AC

XVS10MMW

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XVS
	·
Product or Component Type	Siren
Device short name	XVS
Color	White
Signalling type	2 tones siren
[Us] rated supply voltage	230 V AC
Noise level	106 dB continuous or intermittent tone)1 m

Complementary

Material	PC: body	
Net Weight	2.2 lb(US) (1 kg)	
Marking	CE	
[Uimp] rated impulse withstand voltage	4 kV	
Current consumption	40 mA 230 V	
Clamping Connection Capacity	<= 1 x 1.5 mm²	
Electrical connection	Cable 0.30.3 in (6.58.5 mm)	
Width	4.5 in (114 mm)	
Height	4.5 in (114 mm)	
Depth	6.03 in (153.2 mm)	

Environment

Standards	IEC 60947-1
	IEC 60947-5-1
Protective treatment	TC
Ambient Air Temperature for Storage	-31158 °F (-3570 °C)
Ambient Air Temperature for Operation	-22122 °F (-3050 °C)
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP53

Ordering and shipping details

Category	US100XV22617
Discount Schedule	00XV

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	3389119045360	
Returnability	No	
Country of origin	ID	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	7.68 in (19.500 cm)	
Package 1 Width	5.51 in (14.000 cm)	
Package 1 Length	5.51 in (14.000 cm)	
Package 1 Weight	2.738 lb(US) (1.242 kg)	
Unit Type of Package 2	S04	
Number of Units in Package 2	8	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	15.75 in (40.000 cm)	
Package 2 Length	23.62 in (60.000 cm)	
Package 2 Weight	24.491 lb(US) (11.109 kg)	
Unit Type of Package 3	P06	
Number of Units in Package 3	32	
Package 3 Height	29.53 in (75.000 cm)	
Package 3 Width	23.62 in (60.000 cm)	
Package 3 Length	31.50 in (80.000 cm)	
Package 3 Weight	118.962 lb(US) (53.960 kg)	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	16
Environmental Disclosure	Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Fe0ee3ab-dd49-4abe-bd8e-c49754e2c442
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again


○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Dimensions Drawings

Siren

Dimensions





Technical Illustration

Dimensions




Image of product / Alternate images

Alternative





