

Socket, General Purpose Relays, for 750H/750 relays, DPDT, 8 pins, screws clamp terminals, 16A, 300V

70-750DL8-1

Product availability: Stock - Normally stocked in distribution facility

Main

Product Range	Legacy	
Product Type	Socket	
Product Compatibility	relay 750XCXR relay 750XCXH suppressor module 70-ASMM diode 70-ASMD signalling device 70-ASMLG suppressor module 70-ASMR jumper wire 16-750CBJ-1	
Number of Terminals	8	
Switch Function	DPDT	
Contact Composition	2 NO + 2 NC	

Complementary

Rated Current	16 A	
[Ue] rated operational voltage	300 V	
Contact Terminal Arrangement	Mixed	
Connections Terminals	screw clamp terminals solid for output screw clamp terminals stranded for output	
Tightening Torque	Chassis 0.8 N.m, AWG 14AWG 12, copper Screw 1 N.m	
Fixing Mode	By screw M3.5, M3.5 panel Clip-on 35 mm DIN rail	
Shape of Screw Head	Combination roundhead	
Product Weight	2.1 oz (60 g)	
Width	1.4 in (36 mm)	
Depth	2.9 in (72.7 mm)	

Environment

Ambient Air Temperature for Storage	-40221 °F (-40105 °C)
Ambient Air Temperature for Operation	-40131 °F (-4055 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10CP221127	
Discount Schedule	0CP2	
GTIN	3606480278006	
Returnability	Yes	
Country of origin	TW	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	3.05 in (7.75 cm)	
Package 1 Width	1.42 in (3.6 cm)	
Package 1 Length	1.42 in (3.6 cm)	
Package 1 Weight	2.1 oz (60.0 g)	
Unit Type of Package 2	CAR	
Number of Units in Package 2	10	
Package 2 Height	3.27 in (8.3 cm)	
Package 2 Width	2.91 in (7.4 cm)	
Package 2 Length	7.64 in (19.4 cm)	
Package 2 Weight	26.1 oz (740.5 g)	
Unit Type of Package 3	BB1	
Number of Units in Package 3	100	
Package 3 Height	16.22 in (41.2 cm)	
Package 3 Width	9.06 in (23.0 cm)	
Package 3 Length	16.10 in (40.9 cm)	
Package 3 Weight	33.07 lb(US) (15.0 kg)	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	1	

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
China RoHS Regulation	China RoHS declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No


Dimensions Drawings

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams



MODULE