# 8910DPA93V14

Contactor, Definite Purpose, 90A, 3 pole, 50 HP at 575 VAC, 3 phase, 24/24 VAC 50/60 Hz coil, open



# Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	90 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

### Complementary

Maximum Horse Power Rating	7.5 Hp 115 V AC, 1 phase	
	20 Hp 230 V AC, 1 phase	
	30 Hp 230 V AC, 3 phase	
	50 Hp 460 V AC, 3 phase	
	50 hp 575 V AC, 3 phase	
Locked rotor rated current	540 A 277 V AC	
	450 A 460 V AC	
	360 A 575 V AC	
[Ue] rated operational voltage	600 V AC	
[Uc] control circuit voltage	24 V AC 50/60 Hz	
Phase	3 phase	
Electrical Connection	Box lugs	
	Quick connect terminals	

#### Environment

Product Certifications	UL Recognized CSA	:

#### Ordering and shipping details

ordering and emphring details	
Category	21349-8910 DPA 9_(90 AMP)
Discount Schedule	CP1B
GTIN	785901024583
Nbr. of units in pkg.	1
Package weight(Lbs)	3.62 lb(US) (1.642 kg)
Returnability	Yes
Country of origin	CN

#### **Packing Units**

Unit Type of Package 1	PCE	
Package 1 Height	5.80 in (14.732 cm)	
Package 1 width	5.60 in (14.224 cm)	
Package 1 Length	7.00 in (17.78 cm)	

# Offer Sustainability

REACh Regulation	REACh Declaration	
EU RoHS Directive	Compliant EPEU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	₫Yes	
China RoHS Regulation	China RoHS Declaration	

# Contractual warranty

Warranty 18 months	Warranty	
--------------------	----------	--