

Customer Specification

PART NO. 892007

Construction

	Diameters (In)	
1) Component 1	1 X 1 HOOKUP	
a) Conductor	20 (7/28) AWG Tinned Copper	0.038
b) Insulation	0.016" Wall, Nom. PVC	0.070+/- 0.002
(1) Print	20 AWG EXXXXX RU AWM STYLE 1569 105C 300V VW-1 OR AWM 1007 LLXXXXX CSA AWM I A/B 105C 300V FT1 OR TR-64 90C <i>[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]</i>	
(2) Color(s)	WHITE, BLACK, RED, GREEN, YELLOW, BLUE, BROWN ORANGE, SLATE, VIOLET	

Applicable Specifications

1) UL	AWM/STYLE 1569	105°C / 300 V _{RMS}
	AWM/STYLE 1007	80°C / 300 V _{RMS}
	VW-1	
2) CSA International	AWM I A/B	105°C / 300 V _{RMS}
	FT1	
	TR-64	90°C

Environmental

1) EU Directive 2011/65/EU(RoHS2), EU Directive 2015/863/EU (RoHS3):	
	All materials used in the manufacture of this part are in compliance with European Directive 2011/65/EU and the amending Directive 2015/863/EU of 4 June 2015 regarding the restriction of use of certain hazardous substances in electrical and electronic equipment.
2) REACH Regulation (EC 1907/2006):	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-40 to 105°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	8.7 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	300 V _{RMS}
2) Inductance	0.05 μH/ft, Nominal
3) Conductor DCR	10.1 Ω/1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 5000 FT	12 x 5.94 x 5 Continuous length
b) 1000 FT	6.5 x 4 x 2.5 Continuous length
c) 500 FT	6.5 x 2 x 1.9 Continuous length
d) 100 FT	2.75 x 2 x 1.125 Continuous length
e) Bulk(Made-to-order)	
	<i>[Spool dimensions may vary slightly]</i>
Notes:	
a) Certain colors and put-up combinations may only be available by special order, minimums may apply.	

www.alphawire.com

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374

Tel: 1-800-52 ALPHA

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure the accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 892007

892007, RoHS-Compliant Commencing With 7/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above, including all packaging materials, is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with UK - RoHS. The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014. This product is also in compliance with China RoHS 2 per GB/T 26572-2011.

Substance

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) , Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering 9/30/2025

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374
Tel: 1-908-925-8000