

! To be discontinued

module XPSOT - stop at top dead center with automatic overtravel - 115 V AC

XPSOT3444

- ! Discontinued on: Dec 27, 2024
- ! To be end-of-service on: Dec 31, 2025

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Preventa Safety automation	
Product or Component Type	Preventa safety module	
Safety module name	XPSOT	
Safety module application	Safety stop with automatic overtravel monitoring and control	
Function of module	Safety stop with automatic overtravel monitoring and control	
Safety level	Can reach PL e/category 4 ISO 13849-1 Can reach SILCL 3 IEC 62061	
Safety reliability data	MTTFd = 60.9 years ISO 13849-1 DC = 099 % ISO 13849-1 PFHd = 1.33E-8 1/h IEC 62061	
[Us] Rated Supply Voltage	115 V AC - 1515 %	
Output type	Relay, 3 NO, volt-free	
Number of additional circuits	4 solid state outputs	
Enclosure Type	Removable	

Complementary

Supply frequency	50/60 Hz	
Power Consumption in VA	12 VA	
Input protection type	Internal, electronic	
Breaking capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output	
Breaking capacity	10 mA 48 V solid state output circuit 20 mA 24 V solid state output circuit 1.5 A 24 V DC-13)50 ms relay output	
[Ith] conventional free air thermal current	2.5 A	
Associated fuse rating	4 A gG relay output EN/IEC 60947-5-1, DIN VDE 0660 part 200	
Minimum output current	10 mA relay output	
Minimum output voltage	17 V relay output	
Maximum response time on input open	20 ms	
[Ui] rated insulation voltage	300 V 2)IEC 60647-5-1, DIN VDE 0110 part 1	
[Uimp] rated impulse withstand voltage	4 kV III IEC 60647-5-1, DIN VDE 0110 part 1	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Local signalling	4 LEDs	
Enclosure Material	Polycarbonate	
Number of terminal blocks	42	
Connections - terminals	Captive screw clamp terminals, $2 \times 0.52 \times 1.5 \text{ mm}^2$ with cable end Captive screw clamp terminals, $2 \times 2.5 \text{ mm}^2$ without cable end	
Mounting Support	35 mm symmetrical DIN rail	
Depth	4.6 in (118 mm)	
Height	2.9 in (73 mm)	
Width	7.9 in (200 mm)	
Product Weight	2.4 lb(US) (1.1 kg)	

Environment

Standards	IEC 692 IEC 60947-5-1 IEC 60204-1	
Product Certifications	CSA UL TÜV	
IP degree of protection	IP10 terminals)IEC 60529 IP40 enclosure)IEC 60529	
Ambient air temperature for operation	14131 °F (-1055 °C)	
Ambient Air Temperature for Storage	-13185 °F (-2585 °C)	

Ordering and shipping details

Category	US1SAF222477	
Discount Schedule	SAF2	
GTIN	3389110724752	
Returnability	No	
Country of origin	ID	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	3.54 in (9.0 cm)	
Package 1 Width	8.86 in (22.5 cm)	
Package 1 Length	5.71 in (14.5 cm)	
Package 1 Weight	2.701 lb(US) (1.225 kg)	
Unit Type of Package 2	S03	
Number of Units in Package 2	9	
Package 2 Height	11.81 in (30.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	25.97 lb(US) (11.78 kg)	

Contractual warranty

Warranty

Jun 29, 2025

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	528
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.