

MN delay unit, MasterPact NT/NW, ComPacT NS, adjustable time delay 0.5s/3s, 200/250VDC, 200/250VAC 50/60Hz, spare part

33682

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	MN delay unit	
Product or Component Type	Time delay relay	
Device Application	Control	
Range compatibility	Masterpact MasterPact NT	
	Masterpact MasterPact NW	
	ComPact ComPact NSX	
	ComPact ComPact NS630b1600	
	ComPact ComPact NS1600b3200	
	PowerPact PowerPact Multistandard	
	ComPact ComPact NSXm	
	ComPact ComPact NSX DC	
	Masterpact MasterPact NW UL 489	
	Masterpact MasterPact NT UL 489	
	Masterpact MasterPact NW DC	
Voltage release type	Undervoltage release	
[Uc] control circuit voltage	200250 V AC 50/60 Hz	
	200250 V DC	

Complementary

Impulse duration	200 ms
Time delay range	0.53 s
Threshold tripping voltage	0.350.7 Un open 0.85 Un close
Supply holding power	4.5 VA
Supply inrush power	200 VA
Mounting Mode	External mounting
Response time	0.5 s 1 s 1.5 s 3 s
Accessory / separate part category	Spare part Compact NS630b1600 Spare part Compact NS1600b3200

Ordering and shipping details

Category	US10NET01081
Discount Schedule	0NET
GTIN	3303430336822
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin US

Packing Units

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.54 in (9.000 cm)
Package 1 Width	3.15 in (8.000 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	6.152 oz (174.400 g)
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	14.722 lb(US) (6.678 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Carbon footprint (kg CO2 eq, Total Life cycle)	4	
Environmental Disclosure	Product Environmental Profile	

Use Better

Recycled metal content at CR level	0
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	6d7ed1bf-0416-4b0a-870a-811eb3730f6d
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.