

Die cast empty control station, Harmony XAP, XB2 SL, zinc alloy, grey, M20, 1 cut out 22mm, 80x80x77mm, UL cULus

XAPD1501

Product availability: Stock - Normally stocked in distribution facility

## Main

Range of Product	Harmony XAP					
Product or Component Type	Die-cast empty control station					
Device short name	XAPD					
Product destination	For Ø 22 mm control and signalling units					
Product front plate size	80 x 80 mm					
Usable depth	2.9 in (74.5 mm)					
Number of cut-out	1 cut-out					
Colour of base of enclosure	Grey RAL 7035)					
Colour of cover	Grey RAL 7035)					
Material	Die cast zinc					
Sale per indivisible quantity	1					
IP degree of protection	IP65 EN/IEC 60529 and EN/IEC 60947-5-1 IP66 EN/IEC 60529 and EN/IEC 60947-5-1 IP69 EN/IEC 60529 and EN/IEC 60947-5-1					

# Complementary

Number of vertical rows	1
Number of horizontal rows	1
Cut-out dimensions	Ø 22 mm
Control station type	Metal
Cable entry	2 x cable gland ISO
Thread type	M20 x 1.5
CAD overall width	3.1 in (80 mm)
CAD overall height	3.1 in (80 mm)
CAD overall depth	3.03 in (77 mm)
Net Weight	1.334 lb(US) (0.605 kg)

# **Environment**

Protective treatment	TC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical shock protection class	Class I conforming to IEC 61140				
Degree of protection	UL type 4 UL 50 E UL type 4X UL 50 E				
IK degree of protection	IK07 IEC 62262				
Resistance to chemical agents	Special treatment can be obtained on request				
Product Certifications	UL cULus EAC				

# Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
GTIN	3389110001044
Returnability	Yes
Country of origin	MA

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.70 in (9.400 cm)
Package 1 Width	3.35 in (8.500 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	27.619 oz (783.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	12
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	21.083 lb(US) (9.563 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	192
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	365.474 lb(US) (165.776 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	5
Environmental Disclosure	Product Environmental Profile

## **Use Better**


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

# **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

# **Dimensions Drawings**

## **Dimensions and Fixing**



(1): 1 hole, with blanking plug (protrusion 6 mm/0.24 in.), for cable gland ISO M20 x 1.5


(2): 1 hole, without blanking plug, for cable gland ISO M20 x 1.5

(3): 2 x Ø 5.6 mm/0.22 in. holes, depth 19 mm/0.75 in.

P: Usable depth

a b		С		G		Н		Ρ .			
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	80	3.15	77	3.03	50	1.97	65	2.56	74.5	2.93

1 hole in the center, Cut-out interaxis 22.5 mm  $\pm 0.2$  mm / 0.885 in.  $\pm 0.0078$  in. dimensions (vertical mounting)



b1 Vertical interaxis: In the center of the box

b2 Horizontal interaxis: In the center of the box