

Contact block, Harmony XAC, double contact, latching, single speed, front mounting, 2NO

XENG3781

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XAC	
Product or Component Type	Contact block	
Component name	XENG	
Electrical circuit type	Control circuit	
Contact block application	Single speed	
Contact block type	Double	
Type of operator	Latching	
Product Compatibility	XACA	
Contacts type and composition	2 NO	
Mounting of block	Front mounting	
Contact operation	Slow-break	

Complementary

Connections - terminals	Screw clamp terminals, 1 x 0.51 x 2.5 mm 2 without cable end Screw clamp terminals, 1 x 0.52 x 1.5 mm 2 with cable end		
Mechanical durability	1000000 cycles		
Contact code designation	A600 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A IEC 60947-5-1 appendix A		
[Ithe] conventional enclosed thermal current	10 A		
[Ui] rated insulation voltage	600 V 3)IEC 60947-1		
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-1		
Maximum resistance across terminals	25 MOhm		
operating force	15 N		
Short-circuit protection	10 A fuse protection cartridge gG		
Rated operational power in W	40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendic C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C		
Terminals description ISO n°1	(13-14)NO B		
Terminals description ISO n°2	(13-14)NO B		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-5-1	
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock resistance	100 gn IEC 60068-2-27	
Overvoltage category	Class II conforming to IEC 61140	

Ordering and shipping details

Category	US10CS222466	
Discount Schedule	0CS2	
GTIN	3389110645866	
Returnability	Yes	
Country of origin	US	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	1.38 in (3.5 cm)	
Package 1 Width	1.57 in (4.0 cm)	
Package 1 Length	2.36 in (6.0 cm)	
Package 1 Weight	3.2 oz (90.0 g)	
Unit Type of Package 2	S01	
Number of Units in Package 2	50	
Package 2 Height	5.91 in (15.0 cm)	
Package 2 Width	5.91 in (15.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	10.4 lb(US) (4.7 kg)	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances		
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
REACh Regulation	REACh Declaration	
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Use Again

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.