

single function relay, Harmony Timer Relays, 5A, 2CO, 0.1s..100h, on delay, 230V AC

REXL2TMP7

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony Timer Relays	
Fixing mode	Plug-in (socket)	
Product or Component Type	Miniature timing relay	
Discrete output type	Relay	
Contacts type and composition	2 C/O	
Component name	REXL	
Time delay type	Power on-delay	
Time delay range	10100 h 110 min 110 h 0.11 s 660 min 660 s 110 s	
Width	0.8 in (21 mm)	

Complementary

Contacts material	Cadmium free	
[Us] rated supply voltage	230 V AC 50/60 Hz	
Voltage range	0.851.15 Us	
Line Rated Current	5 A AC	
Repeat accuracy	+/- 0.5 %	
Setting accuracy of time delay	10 % at full scale 25 °C IEC 61812-1	
Time delay type	Power on-delay - A- Power on-delay relay	
Temperature Drift	0.05 %/°C	
maximum reset time	250 ms after time delay, on de-energisation 50 ms during time delay, on de-energisation	
Voltage drift	+/- 0.2 %/V	
Maximum switching capacity	4 x 5 A	
maximum temporary permissible current	10 A < 10 s	
minimum switching current	100 mA	
Electrical durability	100000 cycles 250 V AC resistive	
Mechanical durability	10000000 cycles	
maximum power consumption	3 VA	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ui] rated insulation voltage	250 V IEC 255 Group C 250 V VDE 0010	
Output overvoltage protection	2 J	
Surge withstand	2 kV IEC 61000-4-5 level 3	
Creepage distance	4 kV/3 IEC 60664-1	
Local signalling	1 LED (red) for output in operation 1 LED (yellow) for power ON	
Function available	A- Power on-delay relay-2 C/O	
Control Type	Without test button	
Shape of pin	Flat	
Number of functions	1	
Net Weight	0.11 lb(US) (0.05 kg)	

Environment

Immunity to microbreaks	5 ms	
Dielectric strength	2 kV 1 mA/1 minute 50 Hz IEC 60601-1 2 kV 1 mA/1 minute 50 Hz IEC 61812-1	
Standards	IEC 60601-1 89/336/EEC IEC 61000-6-2 EN 50081-2 IEC 61812-1 73/23/EEC IEC 60601-2 93/68/EEC	
Product Certifications	UL cUL	
Ambient Air Temperature for Operation	-4140 °F (-2060 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
IP degree of protection	IP50 conforming to IEC 60529	
Vibration resistance	0.35 mm (f= 1055 Hz) conforming to IEC 60068-2-6	
Relative Humidity	95 % without condensation IEC 60068-2-6	
Resistance to electrostatic discharge	6 kV in contact IEC 61000-4-2 level 3 8 kV in air IEC 61000-4-2 level 3	
Resistance to electromagnetic fields	9.1 V/m (10 V/m) IEC 61000-4-3 level 3	
Resistance to fast transients	2 kV IEC 61000-4-4 level 3	
Immunity to radioelectric fields	10 V 0.1580 MHz)IEC 61000-4-6 level 3	
Immunity to voltage dips	>= 95 % / 1 s IEC 61000-4-11 30 % / 10 ms IEC 61000-4-11 60 % / 100 ms IEC 61000-4-11	
Disturbance radiated/conducted	Class B EN 55022 (EN 55011 group 1)	

Ordering and shipping details

Category	US10CP222370	
Discount Schedule	0CP2	
GTIN	3389119400053	
Returnability	Yes	
Country of origin	ID	

Packing Units

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.18 in (3.0 cm)
Package 1 Length	2.95 in (7.5 cm)
Package 1 Weight	1.8 oz (50.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	48
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	5.745 lb(US) (2.606 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	86
Environmental Disclosure	Product Environmental Profile

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1b9c3411-e0e2-4832-adc7-e6e2a8e06cab
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings

Width 21 mm



Product data sheet

REXL2TMP7

Connections and Schema

Terminal Referencing



Product data sheet

REXL2TMP7

Technical Description

Function A : Power on Delay Relay

Description


The timing period T begins on energisation. After timing, the outputs close. 2 Timed C/O Contacts $\,$



Product data sheet


REXL2TMP7

Legend



Technical Illustration

Dimensions







Offer Marketing Illustration

Product benefits / Features

10

Technical Benefits

Harmony Timer Relay



Offer Marketing Illustration

Product benefits / Features



Image of product / Alternate images

Alternative













Image of product in real life situation

