

Time delay auxiliary contact block, TeSys Deca, 1NO + 1NC, off delay 0.3-3s, front, spring terminals

LADR03

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys TeSys Deca	
Product name	TeSys Deca	
Product or Component Type	Time delay auxiliary contact block	
Range compatibility	TeSys Deca CAD TeSys Deca LC1D	
Mounting Location	Front	
Pole contact composition	1 NO + 1 NC	
Contacts operation	Time delay	
Timer type	Off delay	
Time delay range	0.33 s	
[Ue] rated operational voltage	690 V AC 25400 Hz	
[le] rated operational current	6 A at 120 V AC-15 1.04 A at 690 V AC-15 0.55 A at 125 V DC-13 0.1 A at 600 V DC-13	
[Ui] rated insulation voltage	690 V IEC 60947-5-1 600 V UL 60947-5-1 600 V CSA C22.2 No 60947-5-1	
[Ith] conventional free air thermal current	al 10 A (at 140 °F (60 °C))	
Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5 EN 50012 IEC 60335-1:Clause 30.2 IEC 60335-2-40:Annex JJ UL 60335-2-40:Annex JJ	
Product Certifications	IECEE CB Scheme UL CSA CCC EAC UKCA	

Complementary

Irms rated making capacity	140 A AC	
	250 A DC	
Permissible short-time rating	100 A 140 °F (60 °C) 1 s	
	120 A 140 °F (60 °C) 500 ms	
	140 A 140 °F (60 °C) 100 ms	
Protection type	GG fuse 10 A	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mechanical durability	5 Mcycles	
Minimum switching current	5 mA	
Minimum switching voltage	17 V	
Non-overlap time	1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact	
Insulation resistance	> 10 MOhm	
Connections - terminals	spring terminals 2 0.004 in² (2.5 mm²)flexible without cable end spring terminals 2 0.004 in² (2.5 mm²)rigid	
Height	1.9 in (48 mm)	
Width	1.7 in (44 mm)	
Depth	2.4 in (61 mm)	
color	Dark grey	

Environment

Environmental characteristic	Normal environment	
IP degree of protection	IP20 conforming to IEC 60529	
Protective treatment	TH IEC 60068	
Ambient Air Temperature for Storage	-76176 °F (-6080 °C)	
Ambient Air Temperature for Operation	-40158 °F (-4070 °C)	
Operating altitude	9842.52 ft (3000 m)	

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0112
GTIN	3389110821642
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.05 in (5.2 cm)
Package 1 Width	2.56 in (6.5 cm)
Package 1 Length	1.85 in (4.7 cm)
Package 1 Weight	2.8 oz (79.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.05 in (5.2 cm)
Package 2 Width	5.31 in (13.5 cm)
Package 2 Length	9.45 in (24.0 cm)
Package 2 Weight	28.3 oz (802.0 g)
Unit Type of Package 3	S03

Number of Units in Package 3	140
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	26.273 lb(US) (11.917 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	4
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	116c8fe4-0538-43fb-9c58-cfc8259b5fbc
REACh Regulation	REACh Declaration
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.