





▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	ON	ON
2-3, 5-6	2-3, 5-4	2-1, 5-4



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: $x.x = \pm 0.4$
 $x.xx = \pm 0.25$
- TERM. NUMBERS FOR REFERENCE ONLY
- RATING: 2 AMPS @250VAC
 5 AMPS @120VAC OR 28VDC
- FIXED TERM. & MOVING CONTACT:
 COPPER ALLOY W/SLIVER PLATE OVER NICKEL PLATE
- ELECTRICAL LIFE: 40,000 make and break cycles at full load
- INSULATION RESISTANCE: 1,000M OHM MIN.
- DIELECTRIC STRENGTH: 1000V RMS @ SEA LEVEL
- OPERATING TEMP: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER
- ▲ 11. CONTACT MATERIAL: SILVER



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100113	Release	05/13/21	MW	100DP6T3B2VS3QE				100116599
					SCALE	DATE	DR	DWG	REV
					2:1	5/11/2021	MW	T126071	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED