

Double contact block, Harmony XAC, spring return, single speed, snap action, 3NO

XESD2201

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range of Product	Harmony XAC
Product or Component Type	Contact block
Component name	XESD
Electrical circuit type	Power circuit
Contact block application	Single speed
Contact block type	Double
Type of operator	2 spring return
Product Compatibility	XACB
Mechanical interlocking	With mechanical interlocking
Contacts type and composition	3 NO
Poles description	3-pole
Mounting of block	Front mounting
Contact operation	Snap action

### Complementary

Connections - terminals	Screw clamp terminals, $1 \times 2.5 \text{ mm}^2$ with or without cable end Screw clamp terminals, $2 \times 1.5 \text{ mm}^2$ with or without cable end	
Horizontal fixing centres	1.6 in (40 mm)	
Mechanical durability	1000000 cycles	
[Ithe] conventional enclosed thermal current	20 A	
[Ui] rated insulation voltage	300 VCSA	
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-1	
operating force	32 N	
Short-circuit protection	12 A fuse protection cartridge aM	
Rated operational power in W	3000 W AC-3 240 V 3000 W AC-4 400 V	
Rated power in hp	3 hp 240 V	
Electrical durability	1000000 cycles AC-3, 3000 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 1000000 cycles AC-4, 3000 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 700000 cycles AC-3, 3000 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 700000 cycles AC-4, 3000 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A	
Terminals description ISO n°1	(23-24)NO B (33-34)NO (13-14)NO	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Terminals description ISO n°2	(53-54)NO
•	В
	(63-64)NO
	(73-74)NO
Terminal identifier	(13-14)NO
	(11-12)NC
Net Weight	0.4 lb(US) (0.2 kg)

### **Environment**

Standards	IEC 60947-3 IEC 60947-3 CSA C22.2 No 14	
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock resistance	100 gn IEC 60068-2-27	
Electrical shock protection class	Class II conforming to IEC 61140	

# Ordering and shipping details

Category	US10CS222473	
Discount Schedule	0CS2	
GTIN	3389110644005	
Returnability	Yes	
Country of origin	CZ	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.62 in (9.2 cm)
Package 1 Width	2.99 in (7.6 cm)
Package 1 Length	2.83 in (7.2 cm)
Package 1 Weight	9.2 oz (260.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	15
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	9.39 lb(US) (4.26 kg)

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	2
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

### Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.