









| ▲ SWITCH FUNCTION |        |        |
|-------------------|--------|--------|
| POS. 1            | POS. 2 | POS. 3 |
|                   |        |        |
| (ON)              | OFF    | (ON)   |
| 2-3               | OPEN   | 2-1    |

( ) = DENOTES MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: GOLD
5. RATING: 0.4 VOLT-AMPS (VA) MAX. @ 20V MAX. (AC OR DC)
6. ELECTRIC LIFE: 6,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -40°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.



| REV | ECO NO     | DESCRIPTION       | DATE     | BY | E-SWITCH®              |           |    |         | OBJECT ID |
|-----|------------|-------------------|----------|----|------------------------|-----------|----|---------|-----------|
| G   | ECO-102119 | 100 SERIES UPDATE | 08/01/23 | MR | TITLE 100SP4T6B12VS5RE |           |    |         | 000024097 |
|     |            |                   |          |    | SCALE                  | DATE      | DR | DWG     | REV       |
|     |            |                   |          |    | 2:1                    | 3/13/2007 | TN | T114060 | G         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED