

AR4018SP

APC NetShelter CX, 18U, Soundproof Server Rack Enclosure, 100V to 240V, Grey, 1015H x 750W x 1130D mm



Overview

Presentation	NetShelter CX Enclosure with integrated cooling and noise dampening is ideal for office environments. The cabinet is paired with a shock absorbing pallet, unloading ramp and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).
Lead time	Usually Ships within 8 Weeks

Main

Main Input Voltage	100 V 110 V 115 V 120 V 200 V 208 V 220 V 230 V 240 V
Plug standard	IEC 60320 C14
Number of rack unit	18U
Provided equipment	Key(S) Leveling feet Pallet ramps Reusable packaging Unpacking sheet

Physical

Color	Gray Oak
Height	39.96 in (101.5 cm)
Width	29.53 in (75 cm)
Depth	44.49 in (113 cm)
Net Weight	317.47 lb(US) (144 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	33.94 in (86.21 cm)
Rack Width	19"
Permanent permissible load	700 Lb(US) (317.51 kg) dynamic 1826 lb(US) (828.26 kg) static

Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
-----------------	--------------------------------

Conformance

Standards	EIA-310D UL 2416
-----------	---------------------



Ordering and shipping details

GTIN	731304337881
Package weight(Lbs)	485.02 lb(US) (220 kg)

Packing Units

Package 1 Height	50.39 in (128 cm)
Package 1 width	39.37 in (100 cm)
Package 1 Length	51.18 in (130 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------