





RECOMMENDED P.C. MOUNTING

| SWITCH FUNCTION |        |          |
|-----------------|--------|----------|
| POS. 1          | POS. 2 | POS. 3   |
|                 |        |          |
| (ON)            | OFF    | (ON)     |
| 2-3, 5-6        | OPEN   | 2-1, 4-5 |





(ON) = MOMENTARY



CIRCUIT: DPDT

## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. PLATING MATERIAL: GOLD
5. RATING: 0.4 VOLT-AMPS MAX. @20V MAX. AC OR DC
6. ELECTRIC LIFE: 30,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2011/65/EU (ROHS) COMPLIANT

E-SWITCH MARKING  
OPPOSITE SIDE

E-SWITCH®

|     |        |                              |         |     |
|-----|--------|------------------------------|---------|-----|
| B   | 22706  | UPDATED LAYOUT AND TERMINALS | 2/15/17 | MJR |
| A   | 12824  | RELEASED FOR PRODUCTION      | 2/21/03 | CJB |
| REV | PCR NO | DESCRIPTION                  | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 300AWDP4J1BLKM6RE

SCALE  
2:1DATE  
2/21/2003DR  
CJBDWG  
T302009REV  
B