



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	12 V DC
Main Output Voltage	12 V DC
Rated power in W	38 W
Rated power in VA	140 VA
Battery Type	Li-Ion (Lithium Ion)
Provided Equipment	User Manual

Physical

Height	3.78 in (9.6 cm)
Width	7.40 in (18.8 cm)
Depth	3.78 in (9.6 cm)
Net Weight	1.65 lb(US) (0.75 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Output

Max Configurable Power (Watts)	38 W
--------------------------------	------

Conformance

Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class B
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	23...113 °F (-5...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	24 h

Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Ordering and shipping details

GTIN	731304338741
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.69 in (17 cm)
Package 1 Width	6.10 in (15.5 cm)
Package 1 Length	3.86 in (9.8 cm)
Package 1 Weight	2.25 lb(US) (1.02 kg)
SCC14	10731304338748

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------