

SMX2200HV

APC Smart-UPS X, Line Interactive, 2200VA,
Rack/tower convertible 4U, 208V-230V,
8x C13+2x C19 IEC, SmartSlot, Extended
runtime, Short depth



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	208 V 230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	208 V 230 V
Other Output Voltage	208 V 220 V 240 V
Kw Rating	1980 W
Rated power in VA	2200 VA
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Nb of power socket outlets	8 IEC 320 C13 2 IEC Jumpers 2 IEC 320 C19
Number of rack unit	4U
Cable length	6.56 ft (2.00 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Rack Mounting support rails Smart UPS signalling RS-232 cable User Manual USB cable

General

Number of power module	1750
Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Extended run
Redundant	No

Physical

Color	Black
Height	17.01 in (43.2 cm)
Width	7.01 in (17.8 cm)
Depth	19.02 in (48.3 cm)
Net Weight	85.01 lb(US) (38.56 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	1
USB compatible	Yes

Input

Efficiency at full load	140...280 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1980 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE CSA EAC IRAM RCM VDE
Standards	EN 50091-1 EN 50091-2 EN/IEC 62040-1 EN/IEC 62040-2 FCC Part 15 class A IEC 60950

Environmental

Acoustic level	55 dBA
Heat dissipation	150 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	3...5 year(s)

Battery power in VAh	702 VAh runtime
Battery Charge Power (Watts)	233 W rated
Battery option	SMX120BP 1 2106 VAh SMX120BP 2 3510 VAh SMX120BP 3 4914 VAh SMX120BP 4 6318 VAh SMX120BP 6 9126 VAh SMX120BP 8 11934 VAh SMX120BP 10 14742 VAh

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	1

Surge Protection and Filtering

Surge energy rating	645 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304292609
Package weight(Lbs)	105.23 lb(US) (47.73 kg)

Packing Units

Package 1 Height	12.99 in (33 cm)
Package 1 width	23.07 in (58.6 cm)
Package 1 Length	24.92 in (63.3 cm)
Number of Units in Package 3	6
Package 3 Weight	856.92 lb(US) (388.69 kg)
Package 3 Height	43.50 in (110.49 cm)
Package 3 width	48.00 in (121.92 cm)
Package 3 Length	31.00 in (78.74 cm)
Pallet unit layers	2
Pallet layers	4

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---