





ISOMETRIC



NOTE:


- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- RATINGS: 12mA @24VDC
- CONTACTS: FIXED AND MOVING:
COPPER ALLOY W/GOLD PLATE
- CONTACT RESISTANCE: 50M OHMS MAX (INITIAL)
- INSULATING RESISTANCE: 100M OHMS
- OPERATING LIFE: 500,000 cycles min.
- OPERATING TRAVEL: 2.5MM ± 0.5MM
- ▲ DENOTES CRITICAL PARAMETER.
- OPERATING TEMP.: -10°C TO 60°C
- OPERATING FORCE: 170 +/- 50 GRAMS

RED LED

PARAMETERS	SYMBOL	MAX.	MIN.	TYP.	UNITS
POWER DISSIPATION	P _D	80	--		mW
AVE FORWARD CURRENT	I _{AF}	30	--		mA
PEAK FORWARD CURRENT	I _{PF}	80	--		mA
FORWARD VOLTAGE	V _F	2.8	1.8	2.2	V
REVERSE VOLTAGE	V _R	5	--		V
REVERSE CURRENT	I _R	100	--		μA
EMISSION WAVELENGTH	λ _P			695	nm
LUMINOUS INTENSITY	I _F		0.7	2.2	mcd

GREEN LED

PARAMETERS	SYMBOL	MAX.	MIN.	TYP.	UNITS
POWER DISSIPATION	P _D	100	--		mW
AVE FORWARD CURRENT	I _{AF}	30	--		mA
PEAK FORWARD CURRENT	I _{PF}	120	--		mA
FORWARD VOLTAGE	V _F	2.8	1.9	2.2	V
REVERSE VOLTAGE	V _R	5	--		V
REVERSE CURRENT	I _R	100	--		μA
EMISSION WAVELENGTH	λ _P			570	nm
LUMINOUS INTENSITY	I _F		6.0	15.0	mcd



TITLE 5501MBLKREDGRN

SCALE 1:1

DATE 10/16/2001

DR CJC

DWG XR0104P

REV C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

C	21669	UPDATED AND ADDED NOTES	10/24/14	AS
B	14604	REVISED AND REDRAWN	1/5/05	AR
REV	PCR NO	DESCRIPTION	DATE	BY